




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**  
Connector & Housing Type: **Plug**  
Connector System: **Wire-to-Board**  
Number of Positions: **2**  
Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	1b,2a,2b
Number of Positions	2
Number of Rows	1

Body Features

Primary Product Color	Blue
-----------------------	------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Strain Relief	Without
Locking Latch Between Cavity Number	1&2
Panel Mount Feature	Without
Mating Retention Type	Latch
PCB Mount Retention	Without
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Housing Entry Configuration	Both Ends Closed
Centerline (Pitch)	5 mm [.197 in]

Dimensions

Connector Height	13.9 mm [.547 in]
Connector Length	25.5 mm [1 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

RAST Version	02-G
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Glow Wire

Packaging Features

Packaging Method	Bag
Packaging Quantity	6000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)  
Candidate List Declared Against: JUNE 2024 (241)  
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.




Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 5-1241965-2 2POS STANDARD TIMER HOUSING</p>	 <p>TE Part # 1241961-1 STD TIM HOUSING MKII 2POS</p>	 <p>TE Part # 5-1241983-3 STANDARD TIMER HOUSING MARK II</p>	 <p>TE Part # 2-964983-2 STD TIM GEH 2P</p>
 <p>TE Part # 1241965-2 STD TIMER HOUSING 2POS</p>	 <p>TE Part # 4-1241965-2 STD TIMER HOUSING</p>	 <p>TE Part # 6-1241965-2 2P ST-TIMER GEH</p>	 <p>TE Part # 1241965-4 STANDARD TIMER HSG. WITH EXT. LOCK.</p>



TE Part # 1241965-6  
STD-TIMER GEH 6P

TE Part # 2-1241965-7  
7P ST-TIMER GEH

TE Part # 6-1241983-2  
STANDARD TIMER HOUSING MARK II

TE Part # 8-1241983-2  
STANDARD TIMER HOUSING MARK II

Also in the Series | RAST 5 IDC Connectors

Connector Contacts(12)

Crimp Terminal Housings(39)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(417)

Power Contacts(3)

Rectangular Power Connectors(481)

Standard Edge Connectors(31)

Wire-to-Board Headers & Receptacles (417)

Customers Also Bought

TE Part #1-967584-3  
4POS MOS TAB SEALED COD A

TE Part #794616-6  
FREE HANG DBL ROW HSG 6 POS

TE Part #1102773001  
FLT0111-0.25-9

TE Part #324485  
SPARE WIRE CAP,RED .080-.115 INS.

TE Part #215083-6  
MICRO-MATCH MOW.06P

TE Part #444082-2  
MINI AMP IN SHORT V

TE Part #NB14494001  
VERSAFIT-3/8-0-SP

TE Part #1488991-5  
3POS, MCON 1.2 CB REC 2p TL SEALED





Documents

Product Drawings

STD TIMER HOUSING

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-1241965-2\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1241965-2\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1241965-2\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Product Specification

German

Agency Approvals

VDE Certificate

English