



Technical data

4T-32310C

Single row tapered roller bearings



VISUAL (S)



4T-32310C

Single row tapered roller bearings

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	50 mm
D - External diameter	110 mm
B - Bearing/Inner ring width	40 mm
C - Outer ring width	33 mm
T - Total width	42,25 mm
a - Charge load application point	33,5 mm
rs - Min fillet radius	2,5 mm
r1s - Min fillet radius	2,5 mm
Mass	1,97 kg

PRODUCT PERFORMANCE

C - Dynamic load	178000000 mN
C0 - Static load	220000000 mN
A2 - Rating life coefficient	1
e - Coefficient	0.55
Y0 - Static axial load coefficient	0.6
Y2 - Upper axial load coefficient	1.1
N lim - Oil lubrication limit speed	27600 °/s
N lim - Grease lubrication limit speed	21000 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da min - Min shoulder diameter OR	80,5 mm
--	---------



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

4T-32310C

Single row tapered roller bearings

ABUTMENT

Da max - Max shoulder diameter OR	100 mm
Db min - Min OR shoulder diameter	104 mm
Ca - Min clearance	3 mm
Cb - Min clearance	9 mm
ra max - Max fillet radius	2 mm
r1a - Max fillet radius	2,5 mm

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15