


FULL BODY HARNESS VIT'O

neofeu.com

REF.
NUS77A /P /EX /EXP

*In seul métier l'antichute

CERTIFICATION: EN 361:2002 / EN 1497:2007 / REGULATION: 2016 / 425





Ergonomic and high density back pad

Shoulder straps adjustment pulling downwards

Aluminum front O ring

Water repellent webbing with fall indicator

Tool holders

Padded leg straps with adjustment through automatic buckles



Orange coated back D ring



Automatic aluminum buckles with locking indicator



Activated fall indicator



Water repellent webbing

TECHNICAL SPECIFICATIONS

- Tested to 140 kg
- Water repellent webbing in polyester 44 mm (R≥25 kN)
- Shoulder straps adjustment pulling downwards with steel black epoxy coated quick buckles male/female
- Chest strap 44 mm with automatic front buckle
- Drop indicator showing at 300 daN
- Comfort pads on legs
- Static resistance ≥ 15 kN
- Weight : 1,2 kg Standard models :
- Without back pad Réf. NUS77A
- With back pad Réf NUS77AP

Other models available on request:

- Back extension strap of 300 mm Réf. NUS77AEX
- Back pad + back extension strap Réf. NUS77AEXP

USE

Full body harness to use in case of fall hazard. Intended to maintenance works in industry and the construction area.

DESCRIPTION

Full body harness VIT'O comfortable lightweight and safe, fits most of the bodies thanks to its high performance adjusting and locking systems.

