


# Data sheet

## chainflex® CF6



Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
 ● Oil-resistant ● Flame retardant



1. Outer jacket: Pressure extruded, oil-resistant PVC mixture
2. Overall shield: Extremely bending-stable braid made of tinned copper wires
3. Inner jacket: Pressure extruded, gusset-filling PVC mixture
4. CFRIP: Tear strip for faster cable stripping
5. Core insulation: Mechanically high-quality TPE or PVC mixture
6. Conductor: Fine-wire stranded conductor consisting of bare copper wires
7. Strain relief: Tensile stress-resistant centre element
8. 12 cores or more: Bundles with optimised pitch length and pitch direction

**Example image**  
 For detailed overview please see design table

### Cable structure

	<b>Conductor</b>	Finely stranded conductor consisting of bare copper wires (following DIN EN 60228).
	<b>Core insulation</b>	<b>Cores <math>\leq 0.5 \text{ mm}^2</math>:</b> Mechanically high-quality TPE mixture. <b>Cores <math>\geq 0.75 \text{ mm}^2</math>:</b> Mechanically high-quality PVC mixture.
	<b>Core structure</b>	<b>Number of cores <math>&lt; 12</math>:</b> Cores wound in a layer with short pitch length. <b>Number of cores <math>\geq 12</math>:</b> Cores wound in bundles which are then wound around a high tensile strength centre element, all with optimised short pitch lengths and directions. Especially low-torsion structure.
	<b>Core identification</b>	<b>Cores <math>\leq 0.34 \text{ mm}^2</math>:</b> Colour code in accordance with DIN 47100. <b>Cores <math>\geq 0.5 \text{ mm}^2</math>:</b> Black cores with white numbers, one green-yellow core.
	<b>Inner jacket</b>	PVC mixture adapted to suit the requirements in e-chains®.
	<b>Overall shield</b>	Aluminum/Polyester tape and extremely bending-resistant braiding made of tinned copper wires. Coverage approx. 70 % linear, approx. 90 % optical
	<b>Outer jacket</b>	Low-adhesion, oil-resistant PVC mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-4-1). Colour: Moss green (similar to RAL 6005) Printing: white
	<b>CFRIP®</b>	Strip cables faster: a tear strip is moulded into the inner jacket Video ► <a href="http://www.igus.eu/CFRIP">www.igus.eu/CFRIP</a>

„00000 m\*\*\* igus chainflex CF6.--.① ----② 300/500V E310776  
 cRUus AWM Style 2570 VW-1 AWM I/II A/B 80°C 600V FT1 EAC/CTP  
 CE RoHS-II conform [www.igus.de](http://www.igus.de) +++ chainflex cable works +++

\* **Length printing:** Not calibrated. Only intended as an orientation aid.  
 ① / ② Cable identification according to Part No. (see technical table).  
 Example: ... chainflex ... CF6.02.04 ... (4x0.25)C ... 300 V/500 V ...



# Data sheet

## chainflex® CF6








Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
● Oil-resistant ● Flame retardant



Example image  
igus® chainflex® CF6

### Dynamic information

	<b>Bend radius</b>	<b>e-chain® linear</b> <b>flexible</b> <b>fixed</b>	minimum 6.8 x d minimum 5 x d minimum 4 x d
	<b>Temperature</b>	<b>e-chain® linear</b> <b>flexible</b> <b>fixed</b>	+5 °C up to +70 °C -5 °C up to +70 °C (following DIN EN 60811-504) -15 °C up to +70 °C (following DIN EN 50305)
	<b>v max.</b>	<b>unsupported</b> <b>gliding</b>	10 m/s 5 m/s
	<b>a max.</b>		80 m/s <sup>2</sup>
	<b>Travel distance</b>		Unsupported travels and up to 100 m for gliding applications, Class 5



These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

### Guaranteed service life according to guarantee conditions

Double strokes	5 million		7.5 million		10 million	
	< 10 m	≥ 10 m	< 10 m	≥ 10 m	< 10 m	≥ 10 m
Temperature, from/to [°C]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]
+5/+15	7.5	10	8.5	11	9.5	12
+15/+60	6.8	7.5	7.8	8.5	8.8	9.5
+60/+70	7.5	10	8.5	11	9.5	12

Minimum guaranteed service life of the cable under the specified conditions.  
The installation of the cable is recommended within the middle temperature range.

### Electrical information

	<b>Nominal voltage</b>	300/500 V (following DIN VDE 0298-3)
	<b>Testing voltage</b>	2000 V (following DIN EN 50395)



# Data sheet

## chainflex® CF6















Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
 ● Oil-resistant ● Flame retardant



Example image

### Properties and approvals

	<b>UV resistance</b>	Medium
	<b>Oil resistance</b>	Oil-resistant (following DIN EN 50363-4-1), Class 2
	<b>Flame retardant</b>	According to IEC 60332-1-2, CEI 20-35, FT1, WW-1
	<b>Silicone-free</b>	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	<b>UL/CSA</b>	<b>Cores &lt; 0.5 mm<sup>2</sup>:</b> Style 10492 and 2570, 600 V, 80 °C <b>Cores ≥ 0.5 mm<sup>2</sup>:</b> Style 11113 and 2570, 600 V, 80 °C
	<b>NFA</b>	Following NFA 79-2012, chapter 12.9
	<b>EAC</b>	Certificate No. RU C-DE.ME77.B.01254 (TR ZU)
	<b>CTP</b>	Certificate No. C-DE.PB49.B.00416 (Fire protection)
	<b>CEI</b>	Following CEI 20-35
	<b>Lead-free</b>	Following 2011/65/EC (RoHS-II)
	<b>Clean room</b>	According to ISO Class 2. The outer jacket material of this series complies with CF5.10.07 - tested by IPA according to standard DIN EN ISO 14644-1
	<b>CE</b>	Following 2014/35/EU



# Data sheet

## chainflex® CF6




Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
 ● Oil-resistant ● Flame retardant



Example image

### Typical lab test setup for this cable series

Test bend radius R	approx. 38 - 200 mm
Test travel S	approx. 1 - 15 m
Test duration	minimum 2 - 4 million double strokes
Test speed	approx. 0.5 - 2 m / s
Test acceleration	approx. 0.5 - 1.5 m / s <sup>2</sup>



### Typical application areas

- For heavy duty applications, Class 5
- Unsupported travel distances and up to 100 m for gliding applications, Class 5
- Light oil influence, Class 2
- No torsion, Class 1
- Preferably indoor applications, but also outdoor ones at temperatures > 5 °C
- Storage and retrieval units for high-bay warehouses, machining units/package machines, quick handling, indoor cranes



# Data sheet

## chainflex® CF6



Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
● Oil-resistant ● Flame retardant



### Technical tables:

#### Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF6.02.04	(4x0.25)C	7.0	29	61
CF6.02.25	(25x0.25)C	14.5	111	260
CF6.03.05	(5x0.34)C	7.5	37	90
CF6.05.02	(2x0.5)C	7.0	29	77
CF6.05.05	(5G0.5)C	8.5	49	106
CF6.05.07	(7G0.5)C	10.0	64	127
CF6.05.09	(9G0.5)C	12.0	70	153
CF6.05.12	(12G0.5)C	13.0	98	232
CF6.05.18	(18G0.5)C	15.0	145	286
CF6.05.25	(25G0.5)C	17.5	192	399
CF6.07.03	(3G0.75)C	8.0	46	98
CF6.07.04	(4G0.75)C	8.5	56	113
CF6.07.05	(5G0.75)C	9.0	67	128
CF6.07.07	(7G0.75)C	10.5	86	152
CF6.07.12	(12G0.75)C	14.0	128	266
CF6.07.18	(18G0.75)C	17.5	196	400
CF6.07.25	(25G0.75)C	19.5	265	536
CF6.10.03	(3G1.0)C	8.0	54	107
CF6.10.04	(4G1.0)C	9.0	64	116
CF6.10.05	(5G1.0)C	9.5	77	136
CF6.10.07	(7G1.0)C	12.0	103	205
CF6.10.12	(12G1.0)C	15.0	161	319
CF6.10.18	(18G1.0)C	19.0	245	482
CF6.10.25	(25G1.0)C	21.0	322	595
CF6.15.03	(3G1.5)C	9.0	72	122
CF6.15.04	(4G1.5)C	9.5	87	155
CF6.15.05	(5G1.5)C	10.5	105	177
CF6.15.07 <sup>17)</sup>	(7G1.5)C	13.0	146	258
CF6.15.12	(12G1.5)C	17.0	225	375
CF6.15.18	(18G1.5)C	21.0	345	581
CF6.15.25	(25G1.5)C	24.0	462	865
CF6.15.36	(36G1.5)C	30.0	675	1293
CF6.25.04	(4G2.5)C	11.5	131	222

<sup>17)</sup> When using the cables with "7 G 1.5 mm<sup>2</sup>" and "7 G 2.5 mm<sup>2</sup>" minimum bend radius must be 17.5 x d with gliding travel distance ≥ 5 m.

**Note:** The given outer diameters are maximum values and may tend toward lower tolerance limits.  
G = with green-yellow earth core x = without earth core




# Data sheet

## chainflex® CF6



Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
 ● Oil-resistant ● Flame retardant



Example image

### Electrical information

Conductor nominal cross section [mm <sup>2</sup> ]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Maximum current rating at 30 °C (following DIN VDE 0298-4) [A]
0.25	79.0	5
0.34	57.0	7
0.5	39.0	10
0.75	26.0	12
1	19.5	15
1.5	13.3	18
2.5	8.0	26

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.



# Data sheet

## chainflex® CF6



Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
 ● Oil-resistant ● Flame retardant



### Design table

Part No.	Number of cores	Core design	Part No.	Number of cores	Core design
CF6.XX.02	2		CF6.XX.09	9	
CF6.XX.03	3		CF6.XX.12	4x3	
CF6.XX.04	4		CF6.XX.18	6x3	
CF6.XX.05	5		CF6.XX.25	5x5	
CF6.XX.07	7		CF6.XX.36	6x6	



Example image  
 igus® chainflex® CF6

# Data sheet

## chainflex® CF6



Control cable (Class 5.5.2.1) ● For heavy duty applications ● PVC outer jacket ● Shielded  
 ● Oil-resistant ● Flame retardant



Example image

### Colour code in accordance with DIN 47100.

Conductor no.	Colours according to DIN ISO 47100	Conductor no.	Colours according to DIN ISO 47100	Conductor no.	Colours according to DIN ISO 47100
1	white	22	brown-blue	43	blue-black
2	brown	23	white-red	44	red-black
3	green	24	brown-red	45	white-brown-black
4	yellow	25	white-black	46	yellow-green-black
5	grey	26	brown-black	47	grey-pink-black
6	pink	27	grey-green	48	red-blue-black
7	blue	28	yellow-grey	49	white-green-black
8	red	29	pink-green	50	brown-green-black
9	black	30	yellow-pink	51	white-yellow-black
10	violet	31	green-blue	52	yellow-brown-black
11	grey-pink	32	yellow-blue	53	white-grey-black
12	red-blue	33	green-red	54	grey-brown-black
13	white-green	34	yellow-red	55	white-pink-black
14	brown-green	35	green-black	56	pink-brown-black
15	white-yellow	36	yellow-black	57	white-blue-black
16	brown-yellow	37	grey-blue	58	brown-blue-black
17	white-grey	38	pink-blue	59	white-red-black
18	brown-grey	39	grey-red	60	brown-red-black
19	white-pink	40	pink-red	61	black-white
20	white-brown	41	grey-black		
21	white-blue	42	pink-black		

