

Instruction Manual **READ CAREFULLY BEFORE USE**

THE EQUIPMENT

C € 0082

EN 362:1993

SNAP HOOK





AZ 011 steel





AZ 013 light alloy snap hook opening 21 mm



AZ 016 light alloy snap hook opening 20 mm



AZ 012 light alloy snap hook opening 17 mm



AZ 014 light alloy snap hook opening 25 mm



AZ 003 light alloy snap hook opening 20 mm

Snap hooks with double finger locking



AZ 002 steel snap hook opening 17 mm



AXK 10 light alloy snap hook opening 22 mm

AZ 022

steel



opening 50 mm




AZ 023 light alloy big snap hook opening 55 mm



AZ 005 steel snap hook opening 18 mm





Snap hooks with automatic locking 'twist-lock"



AZ 011 steel snap hook





AZ 013 light alloy snap hook opening 21 mm




AZ 111 light alloy snap hook opening 42 mm



AZ 012 light alloy snap hook opening 17 mm



AZ 004 light alloy snap hook opening 20 mm





AZ 015 light alloy snap hook opening 23 mm


The snap hook is a component of the personal protective equipment against falsfrom a heightl which complies with EN362. The snap hook is used to connecting theindividual parts of the fall arrest equipment in the one complete system. The snap hook can be the integral part of the fall arrest equipment component (safety lanyard for example) or can be the independent component of the fall arrest system (as a connector for the fall arresters, working ropes, etc.).

BASIC EQUIPMMENT

- 1 body
- 2 gate
- 3 locking gear










BASIC RULES OF USING THE SNAP HOOK


- before each use, a close visual examination of the snap hook components (body, gate, locking gear) must be carried out in
 respect of mechanical, chemical and thermal defects. The examination must be done by a person who is going to use the snap
 hook. In the case of any defect or doubt of correct condition of the snap hook do not use the snap hook.
- using the snap hook, in connection with fall arrest system, must be compatible with manual instructions of the fall arrest systems and obligatory standards:
- EN361 -for the safety harness;
- EN353-1, EN353-2, EN355, EN354, EN360 -for the fall arrest systems;
- EN341 for the rescue equipment;
- EN358-for the work positioning equipment.
- the snap hooks with manual locking (for example screw locking) shall be acceptable only in cases where the user does not have to
 attach and remove the snap hook many times a working day.
- during use the snap hook must be protected from a contact with acids, solvents, basics, open fire, hot metal drops and sharp edges. If you have any doubts about the conditions where the snap hook will be used, ask the producer.
- structural anchor point to which will be connected the snap hook should be situated above working position and should have static resistance min. 15kN, It is recommended to use certified and marked structural anchor point complied with EN 795.
- before use the fall arrest system, the rescue operation must be introduce to avoid any danger that can happened during using the
 equipment.
- the shape of the structural anchor point should not let self-acting snap hook disconnection see the drawings:





necessarly protect the snap hook gate with locking gear-see the drawings:





CONTENT OF THE SNAP HOOK MARKING

CE mark and identity number of the device — AXK 10


CE mark and identity number of the authorized body responsible for controlling manufacture of the device — CO3/01 (or 2001)

European norm (number/year) — necessity of knowledge the instruction manual before using the device manufacturer — O3/01 (or 2001)

marking of the manufacturer — O3/01 (or 2001)

THE ESSENTIAL PRINCIPLES FOR USERS OF PERSONAL PROTECTIVE EQUIPMENT AGAINST FALLS FROM A HEIGHT

- personal protective equipment shall only be used by a person trained and competent in its safe use.
- personal protective equipment must not be used by a person with medical condition that could affect the safety of the equipment user in normal and emergency use.
- a rescue plan shall be in place to deal with any emergencies that could arise during the work.
- it is forbidden to make any alterations or additions to the equipment without the manufacturer's prior written consent.
- any repair shall only be carried out by equipment manufacturer or his certified representative.
- personal protective equipment shall not be used outside its limitations, or for any purpose other than that for which it is intended.
- personal protective equipment should be a personal issue item.
- before use ensure about the compatibility of items of equipment assembled into a fall arrest system. Periodically check connecting and adjusting of the equipment components to avoid accidental loosening or disconnecting of the components.
- it is forbidden to use combinations of items of equipment in which the safe function of any one item is offected by or interferes with the safe function of another.
- before each use of personal protective equipment it is obligatory to carry out a pre-use check of the equipment, to ensure that it is in a serviceable condition and operates correctly before it is
- during pre-use check it is necessary to inspect all elements of the equipment in respect of any damages, excessive wear, corrosion, abrasion, cutting or incorrect acting, especially take into consideration:
 - in full hody harnesses and belts buckles, adjusting elements, attaching points, webhings, seams, loops;
 - in energy absorbers attaching loops, webbing, seams, casing, connectors;
 - in textile lanyards or lifelines or guidelines rope, loops, thimbles, connectors, adjusting element, splices:
 - in steel lanyards or lifelines or guidelines cable, wires, clips, ferrules, loops, thimbles, connectors, adjusting elements;
 - in retractable fall arresters cable or webbing, retractor and brake proper acting, casing, energy absorber, connector;
 - in guided type fall arresters body of the fall arrester, sliding function, locking gear acting, rivets and screws, connector, energy absorber;
 - in connectors main body, rivets, gate, locking gear acting.
- after every12 months of utilization, personal protective equipment must be withdrawn from use to carry out periodical detailed inspection. The periodic inspection must be carried out by a competent person for periodic inspection. The periodic inspection can be carried out also by the manufacturer or his authorized representative. In case of some types of the complex equipment e.g. some types of retractable fall arresters the annual inspection can be carried out only by the manufacturer or his authorized
- regular periodic inspections are the essential for equipment maintenance and the safety of the users which depends upon the continued efficiency and durability of the equipment.
- during periodic inspection it is necessary to check the legibility of the equipment marking.
- it is essential for the safety of the user that if the product is re-sold outside the original country of destination the reseller shall provide instructions for use, for maintenance, for periodic examination and for repair in language of the country in which the product is to be used.
- personal protective equipment must be withdrawn from use immediately when any doubt arise about its condition for safe use and not used again until confirmed in writing by equipment manufacturer or his representative after corried out the detailed inspection.
- personal protective equipment must be withdrawn from use immediately and destroyed when it have been used to arrest a fall;
- a full body harness is the only acceptable body holding device that can be used in a fall arrest system.
- in full body harness use only attaching points marked with big letter "A" to attach a full arrest system. Marking like "A/2" or a half of "A" means the necessity of attaching a full arrest system to both attaching points together simultaneously. It is strictly forbidden to attach a fall arrest system to the single attaching point marked "1/2" or a holf of "A". See drawings below:



- the anchor device or anchor point for the fall arrest system should always be positioned, and the work carried out in such a way, as to minimise both the potential for falls and potential foll distance. The anchor device/point should be placed above the position of the user. The shape and construction of the anchor device/point shall not allowed to self-acting disconnection of the equipment. Minimal static strength of the anchor device/point is 15 kN. It is recommended to use certified and marked structural anchor point complied with EN795.
- it is obligatory to verify the free space required beneath the user at the workplace before each accusion of use the fall arrest system, so that, in the case of a fall, there will be no collision with the ground or other obstacle in the fall path. The required value of the free space should be taken from instruction manual of used equipment.
- there are many hazards that may affect the performance of the equipment and corresponding safety precautions that have to be observed during equipment utilization, especially: - trailing or looping of lanyards or lifelines over sharp edges,
 - any defects like cutting, abrasion, corrosion,
 - climotic exposure.
 - pendulum falls.
 - extremes of temperature,
 - · chemical reagents.
 - electrical conductivity.
- personal protective equipment must be transported in the package (e.g.: bag mode of moisture-proof textile or foil bag or cases made of steel or plastic) to protect it against damage or
- the equipment can be cleaned without causing adverse effect on the materials in the manufacture of the equipment. For textile products use mild detergents for delicate fabrics, wash by hand or in a machine and rinse in water. Plastic parts can be cleaned only with water. When the equipment becomes wet, either from being in use or when due cleaning, it shall be allowed to dry nuturally, and shall be kept away from direct heat. In metallic products some mechanic parts (spring, pin, hinge, etc.) can be regularly slightly lubricated to ensure better operation. Other maintenance and cleaning procedures should be adhered to detailed instructions stated in the manual of the equipment.
- personal protective equipment should be stored loosely packed, in a well-ventilated place, protected from direct light, ultraviolet degradation, damp environment, sharp edges, extreme temperatures and corrosive or aggressive substances.

ADMISSIBLE TIME OF USE

- The snap hook can be used for 5 years. After this period the device must be withdrawn from use to carry out manufacturer's detailed inspection.
- The manufacturer's inspection can be carried out by:
- -manufacturer
- or person recommended by manufacturer
- or company recommended by manufacturer.

During this inspection will be established admissible time of the snap hook use till next manufacturer's inspection.

The snap hook must be withdrawn from use immediately and destroyed when it have been used to arrest a fall.

IT IS THE RESPONSIBILITY OF THE USER ORGANISATION TO PROVIDE THE IDENTITY CARD AND TO FILL IN THE DETAILS REQUIRED.

THE IDENTITY CARD SHOULD BE FILLED IN BEFORE THE FIRST USE BY A COMPETENT PERSON, RESPONSIBLE INTHE USER ORGANIZATION FOR PROTECTIVE EQUIPMENT.

ANY INFORMATION ABOUT THE EQUIPMENT LIKE PERIODIC INSPECTIONS, REPAIRS, REASONS OF EQUIPMENT'S WITHDRAWN FROM USE SHALL BE NOTED INTO THE IDENTITY CARD BY A COMPETENT PERSON.

THE IDENTITY CARD SHOULD BE STORAGED DURING A WHOLE PERIOD OF EQUIPMENT UTILIZATION.

DO NOT USE THE EQUIPMENT WITHOUT THE IDENTITY CARD.

ALL RECORDS IN THE IDENTITY CARD CAN BE FILLED IN ONLY BY A COMPETENT PERSON.

1111				LA	KU //		
MODEL AND TYPE OF EQUIPMENT							
		REF. NU	JMBER				
SERIAL NUMBER				DATE OF MANUF.			
USER NAME							
			18-22		·		
DATE OF PUTTING INTO OPERATION							PERATION
DATE OF PURCHASE							
PERIODIC EXAMINATION AND REPAIR HISTORY							
	DATE	ENTRY PERIODIC EXAMINATION REPAIRS		NOTED, NAME AND SIGNATURE RRIED OUT OF COMPETENT PERSON NT INFORMATIONS			PERIODIC EXAMINATION NEXT DUE DATE
1						,	·
2							
3	,	,					
4.				·.			

EC type examination carried out by CETE APAVE SUDEUROPE, BP 193, 13322 Marseille, France - 0082 CERTEX UK; Unit C1, Harworth Industrial Estate, Bryans Close, Harworth, Doncaster, DN11 8RY www.certex.co.uk