



Image may differ from product. See technical specification for details.

7003 ACD/P4A

Super-precision, high-capacity, single row angular contact ball bearing

These super-precision, high-capacity, single row angular contact ball bearings, with 25° contact angle, accommodate radial and axial loads acting simultaneously, where the axial load acts in one direction only. They are designed to accommodate heavy loads at relatively high speeds under low to moderate operating temperatures.

- Very high running accuracy
- Very high load carrying capacity
- Relatively high speed and stiffness

Overview

Dimensions

Bore diameter	17 mm
Outside diameter	35 mm
Width	10 mm
Contact angle	25 °

Performance

Basic dynamic load rating	6.5 kN
Basic static load rating	3.1 kN
Attainable speed for grease lubrication	45 000 r/min
Attainable speed for oil-air lubrication	70 000 r/min

Properties


Contact type	Normal contact (two-point contact)
Number of rows	1
Ring type	One-piece inner and outer rings
Design	High-capacity D
Universal matching bearing	No
Matched arrangement	No
Matched condition (axial clearance/ preload)	Not applicable
Tolerance class	P4A
Material, bearing	Bearing steel
Coating	Without
Sealing	Without
Lubricant	None

Logistics

Product net weight	0.037 kg
eClass code	23-05-08-04
UNSPSC code	31171531


Technical specification

Universal matching bearing(s)	No
-------------------------------	----



Dimensions

d	17 mm	Bore diameter
D	35 mm	Outside diameter
B	10 mm	Width
d ₁	22.6 mm	Shoulder diameter of inner ring (large side face)
d ₂	22.6 mm	Shoulder diameter of inner ring (small side face)
D ₁	29.3 mm	Shoulder diameter of outer ring (large side face)
r _{1,2}	min. 0.3 mm	Chamfer dimension
r _{3,4}	min. 0.2 mm	Chamfer dimension
a	11.2 mm	Distance from side face to pressure point



Abutment dimensions

d_a	min. 19 mm	Diameter of shaft abutment
d_b	min. 19 mm	Diameter of shaft abutment
D_a	max. 33 mm	Diameter of housing abutment
D_b	max. 33.6 mm	Diameter of housing abutment

r_a	max. 0.3 mm	Radius of fillet
r_b	max. 0.2 mm	Radius of fillet
d_n	23.7 mm	Position of oil nozzle

Calculation data

Basic dynamic load rating	C	6.5 kN
Basic static load rating	C_0	3.1 kN
Fatigue load limit	P_u	0.132 kN
Attainable speed for grease lubrication		45 000 r/min
Attainable speed for oil-air lubrication		70 000 r/min
Contact angle	α	25 °
Ball diameter	D_w	5.556 mm
Number of rows	i	1
Number of balls (per bearing)	z	12
Reference grease quantity (per bearing)	G_{ref}	0.54 cm ³

PRELOAD AND STIFFNESS (BACK-TO-BACK, FACE-TO-FACE)

Preload, class A	G_A	40 N
Axial stiffness for preload A (sets of two brgs back to back or face to face)		48 N/μm
Preload, class B	G_B	80 N
Axial stiffness for preload B (sets of two brgs back-to-back or face-to-face)		62 N/μm
Preload, class C	G_C	160 N
Axial stiffness for preload C (sets of two brgs back-to-back or face-to-face)		81 N/μm
Preload, class D	G_D	320 N
Axial stiffness for preload D (sets of two brgs back-to-back or face-to-face)		107 N/μm

CORRECTION FACTORS FOR PRELOAD CALCULATION

Correction factor dependent on bearing series and size	f	1.04
Correction factor dependent on contact angle	f_1	0.99
Correction factor, preload class A	f_{2A}	1
Correction factor, preload class B	f_{2B}	1.02
Correction factor, preload class C	f_{2C}	1.05
Correction factor, preload class D	f_{2D}	1.08
Correction factor for hybrid bearings	f_{HC}	1

FACTORS FOR EQUIVALENT BEARING LOAD CALCULATION

Limiting value	e	0.68
Axial load factor (single, tandem)	Y_2	0.87
Axial load factor (single, tandem)	Y_0	0.38
Radial load factor (single, tandem)	X_2	0.41
Axial load factor (back-to-back, face-to-face)	Y_1	0.92
Axial load factor (back-to-back, face-to-face)	Y_2	1.41
Axial load factor (back-to-back, face-to-face)	Y_0	0.76
Radial load factor (back-to-back, face-to-face)	X_2	0.67

Tolerances and clearances

GENERAL BEARING SPECIFICATIONS

- [Tolerances: P4A, P4B, P4, PA9A, P2](#)

PRINCIPLES OF BEARING SELECTION AND APPLICATION

- [Chamfer dimensions](#)
- [Seat tolerances for standard conditions: shafts, housings](#)
- Values for ISO tolerance classes: [shafts, housings](#)
- Speed dependent initial grease fill → [Initial grease fill](#)
- Clamping and fitting forces: [D design](#), [E design](#), [B design](#)
- Designation suffixes H, H1, L and L1 identify variants for [direct oil-air lubrication](#).

FACTORS FOR EQUIVALENT BEARING LOAD CALCULATION

- Note 1: [Single bearings and bearings arranged in tandem](#)
- Note 2: [Bearings paired back-to-back or face-to-face](#)

SPEED REDUCTION FACTORS FOR SPEED CALCULATION

Number of bearings	Arrangement	Designation suffix	Speed reduction factors																	
			for matched sets								for bearings in the series									
			718 .. D, 719 .. E, and 70 .. E								S70 .. W	719 .. A and 70 .. A	719 .. B and 70 .. B				719 .. D, 70 .. D and 72 .. D			
			for preload class										for preload class				for preload class			
			A	L	B	M	C	F	–	–		A	B	C	A	B	C	D		
2	Back-to-back	DB	0,8	–	0,65	–	0,4	–	0,81	0,8		0,83	0,78	0,58	0,81	0,75	0,65	0,4		
	Face-to-face	DF	0,77	–	0,61	–	0,36	–	–	–		0,8	0,74	0,54	0,77	0,72	0,61	0,36		
3	Back-to-back and tandem	TBT	0,69	0,72	0,49	0,58	0,25	0,36	–	–		0,72	0,66	0,4	0,7	0,63	0,49	0,25		
	Face-to-face and tandem	TFT	0,63	0,66	0,42	0,49	0,17	0,24	–	–		0,64	0,56	0,3	0,63	0,56	0,42	0,17		
4	Tandem back-to-back	QBC	0,64	–	0,53	–	0,32	–	–	–		0,67	0,64	0,48	0,64	0,6	0,53	0,32		
	Tandem face- to-face	QFC	0,62	–	0,48	–	0,27	–	–	–		0,64	0,6	0,41	0,62	0,58	0,48	0,27		

For spring-loaded tandem sets, designation suffix DT, a speed reduction factor of 0,9 should be applied.

Compatible products

Aftermarket replacement

Super-precision, high-capacity, universally matchable single row angular contact ball bearing	7003 ACDGA/P4A
---	--------------------------------

More Information

 Product details Designs and variants Markings on bearings and bearing sets General bearing specifications Preload, clearance, and stiffness Loads Attainable speeds Mounting Designation system	 Engineering information Principles of bearing selection and application General bearing knowledge Bearing selection process Bearing failure and how to prevent it	 Tools SimPro Quick SimPro Spindle Bearing Frequency Calculator LubeSelect for SKF greases Heater selection tool Super-precision manager tool
---	---	--



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.