



# TCT AX 230mm x 5 Tpi - 1 pc

## WOOD WITH NAILS: HEAVY DUTY AX™ CARBIDE TEETH DEMOLITION BLADES

- Up to 50x longer life than standard Bi-Metal blades. Carbide teeth deliver long life and extreme durability in the toughest applications. Cuts through hardened screws and fasteners.
- Up to 2x faster than standard Bi-Metal blades. A fast and aggressive 5 Tpi tooth pattern allows for the fastest cutting in nail embedded wood and a wide range of construction materials (wood/nails/bolts/screws/cast iron/asphalt roofing felt shingles).
- Up to 25% more cuts per charge vs. standard Bi-Metal blades. Optimised for use with cordless reciprocating saws.
- FANG TIP™: For faster plunge cutting and reaching into restricted areas.
- NAIL GUARD™: Protects the tooth during nail impacts for increased durability and lifetime.
- Sloped shape: Excellent for plunge cutting and reaching into restricted areas.
- Thick 1.27 mm robust blade body for precise straight cuts.
- 25 mm blade height for improved stability and minimum vibration.
- Best for wood / nails / hardened fastners demolition



Article Number	48475226
Blade length (mm)	230
Max. cutting capacity plastic pipes (mm)	10 - 175
Max. cutting capacity wood (mm)	10 - 175
Max. cutting capacity wood with nails (mm)	10 - 175
Pack quantity	1
Plunge cut	Yes
Ref. No.	S1167XHM
Rescue	Yes
Window cut out	Yes