

Features

- Ideal for use in clean room applications, food and beverage and pharmaceutical industries
- Good low temperature resistance and abrasion resistance
- FDA, USP Class VI , REACH, RoHS and EC 1935/2004 compliant
- Suitable for high and low temperature applications
- Not recommended for use in applications where it would come in contact with ozone, weathering, cleaning chemicals, oils and solvents.

RS PRO White Natural Rubber Sheet

1000mm x 1400mm x 3mm

FDA Approved and USP Class VI

RS Stock No.: 0205483



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The RS PRO Natural Rubber sheet is suitable for a wide range of applications and environments including gaskets and seals in food processing equipment, clean rooms and pharmaceutical industries.

General Specifications

Colour	White
Material	Natural Rubber
Adhesive Backing	No
Suitability	FDA approval for use with food

Mechanical Specifications

Length	1m
Width	1.4m
Thickness	3mm
Elongation	300%
Tensile Strength	5 MPa
Hardness	60 ShA

Operation Environment Specifications

Maximum Operating Temperature	85°C
Minimum Operating Temperature	-45°C