

NON-SPARKING KNIVES

EGA Master Non-Sparking tools are the best alternative for applications in potentially explosive environments.

EGA Master's non-sparking knives are designed for construction and masonry work in explosive environments, ensuring the operator's integrity.



**Presented in
a case!**



1. High cutting capacity knives designed for applications in corrosive environments, such as offshore, mining, firefighting applications, chemical industry, petrochemistry.

2. With a hardness of 311-408 Brinell (Cu-Be) and 241-311 Brinell (Al-Bron).

KNIVES

| COD. | MAT. | COD. | MAT. | L (mm) |  |
|--------------|-------|--------------|---------|--------|---|
| 71613 | Cu-Be | 71614 | Al-Bron | 250 | 90 |

| COD. | MAT. | COD. | MAT. | L (mm) |  |
|--------------|-------|--------------|---------|----------|---|
| 71611 | Cu-Be | 71612 | Al-Bron | 30 x 200 | 70 |

TECHNICAL SPECIFICATIONS

| | | |
|-----------|--------|-----------|
| MATERIAL | Handle | Wood |
| FINISHING | | Varnished |

Cu-Be Beryllium copper
Al-Bron Aluminium bronze