
POWERBRIK WT

POWERBRIK | Compact damp-proof luminaires



Areas of application

- Design suitable for representative areas
- Indoor applications

Product benefits

- High impact resistance
- Suitable for use in damp conditions thanks to high type of protection

Product features

- Type of protection: IP65
- DC operation



Technical data

Electrical data

Operating mode	ECG
Nominal wattage	10 W
Nominal voltage	230 V
Mains frequency	0/50...60 Hz

Photometrical data

Color temperature	4000 K
Luminous flux	900 lm
Light color (designation)	Cool white

Dimensions & weight

Length	160.0 mm
Width	90.0 mm
Height	50.0 mm

Colors & materials

Body material	Polycarbonate (PC)
Product color	Grey
Cover material	Polycarbonate (PC)

Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
---------------------------	--------------

Capabilities

Type of installation	Surface-mounted
Type of connection	Terminal, 2-pole, max. 1,5 mm ²


Certificates & standards

Protection class	II
Type of protection	IP65
Protection against ignition and fire	F


Country specific categorizations

Order reference	72173
-----------------	-------

Light Distribution



LDC typ luminance



LDC typ luminance

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899933965	POWERBRIK WT	Shipping carton box 2	229 mm x 127 mm x 108 mm	3.14 dm ³	832.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.