

Product data sheet

Specifications



STD - DIN - remote control dimmer - 400 W

CCTDD20001

Main

range of product	Acti9
Product name	Acti9 STD
Product or component type	Remote control dimmer
Device short name	STD
Product compatibility	Power regulators designed
Function available	Automatic load type detection

Complementary

Device application	Building
Load type	230 V AC halogen lamp: 40...400 W 230 V AC incandescent lamp: 40...400 W low voltage halogen lamp with electronic transformer: 40...400 W motor: 40...200 W low voltage halogen lamp with conventional transformer: 40...400 W low voltage halogen lamp with toroidal transformer: 40...300 W
Control type	Local control: push-button Remote control: push-button
Power consumption in VA	0.8 VA
Thermal losses	3 W
[Ue] rated operational voltage	230 V AC +/- 10 % at 50 Hz
Protection type	Electronic overload protection Electronic over temperature protection Electronic overvoltage protection Single shot thermal fuse
Mounting support	DIN rail
9 mm pitches	4
Connected auxiliaries	Maximum 25 auxiliary push-buttons without light indication, distance : < 50 m Maximum 5 auxiliary push-buttons with light indication, distance : < 50 m
Connections - terminals	Screw terminals, 2 cable(s) 4 mm² top
Height	85 mm
Width	36 mm
Depth	62 mm
Product weight	80 g

Environment

IP degree of protection	IP20
Standards	EN 60669-2-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Directives	73/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility
Ambient air temperature for operation	0...70 °C
Ambient air temperature for storage	0...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.100 cm
Package 1 Width	9.700 cm
Package 1 Length	9.700 cm
Package 1 Weight	136.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Height	19.600 cm
Package 2 Width	30.200 cm
Package 2 Length	41.000 cm
Package 2 Weight	3.652 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	679a8b51-f3fb-4380-a88d-59b4cb86573e
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins