

Product data sheet

Specifications



APC Smart-UPS On-Line, 1000VA,
Lithium-ion, Rackmount 4U, 230V,
8x C13 IEC outlets, SmartSlot,
Extended long runtime, Rail kit
included

SRTL1000RM4UXLI

ⓘ Discontinued

Overview

Presentation	High density, double-conversion on-line power protection with long runtime.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Product or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V
Main Output Voltage	230 V
Other Output Voltage	220 V
Kw Rating	900 W
rated power in VA	1000 VA
Input Connection Type	IEC 60320 C14
output connection type	8 IEC 60320 C13
Number of rack unit	4U
Cable length	6 ft (1.8 m)
Number of cables	1
Range of Product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph
Battery Type	Li-Ion (Lithium Ion)
Battery Voltage	48V
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Battery life	5...10 year(s)
Battery Charge Power (Watts)	103 W rated

General

Number of power module filled slots	0
-------------------------------------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of power module free slots	0
product web sub-family	Lithium Ion
Redundant	No
Topology	Double Conversion Online

Physical

color	Black with silver front bezel
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	22.05 in (56 cm)
Net Weight	30.2 lb(US) (13.7 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal Vertical

Input

Efficiency at full load	160...275 V
Input Frequency	40 - 70 Hz auto-sensing

Output

Bypass type	Built-in Bypass
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	900 W
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE UK PSTI
Marking	CE Mark

Environmental

Acoustic level	50 dBA
Online Thermal Dissipation	400 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Emergency Power Off (EPO)	Yes
Free slots	1
Alarm	Audible and visible alarms : prioritized by severity

Surge Protection and Filtering

Surge energy rating	340 J
---------------------	-------

Ordering and shipping details

GTIN	731304508939
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.65 in (24.5 cm)
Package 1 Width	23.62 in (60 cm)
Package 1 Length	31.89 in (81 cm)
Package 1 Weight	46.3 lb(US) (21 kg)

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Compliant with Exemptions

SCIP Number

8519b6fb-f7a9-44f8-be44-5dee68362126

REACH Regulation

[REACH Declaration](#)

Energy efficiency

Product contributes to saved and avoided emissions

Yes

Use Again

Repack and remanufacture

Circularity Profile

[End of Life Information](#)

Removable battery

User replaceable

Take-back

No

Image of product / Alternate images

Alternative







