




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (2.59% in component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 1520237-9
8910K13=7323 BASIC W/LUBE 632-



TE Part # 1-1520237-1
8910K207=TOOL HANDLE SWITCH




TE Part # 1-1520237-0
8910K201=8 AMP TOGGLE "T" RATE



TE Part # 1520237-8
8909K12=7320K3 W/1 15-192 & 1

Customers Also Bought



TE Part #4-2176400-6
3540 75R 1%



TE Part #4-641435-2
12P MTA156 CONN ASSY ORNG



TE Part #1609112-8
10CS1 M0=F7803



TE Part #2-2176230-2
3522 47R 5% 3W




TE Part #6-1393211-2
T92P7A22-240



TE Part #3-640442-3
03P MTA100 CONN ASSY BLU



TE Part #1-2176070-5
3521 39R 1% 2W



TE Part #1-640550-4
14P MTA100 COVER



TE Part #9-6609955-2
PE0S0D000=C4906



TE Part #5-1393123-2
KHU-17D16-24=KH

Documents

Product Drawings

7320K3=8 AMP TOGGLE SWITCH

English

CAD Files

3D PDF

English



Customer View Model
[ENG_CVM_1520237-2_E.3d_igs.zip](#)
English

Customer View Model
[ENG_CVM_1520237-2_E.3d_stp.zip](#)
English

Customer View Model
[ENG_CVM_1520237-2_E.2d_dxf.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL](#)
English

[UL](#)
English

[UL](#)
English