

# EEM-PM157-SLP - Measuring device



1269236

<https://www.phoenixcontact.com/in/products/1269236>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Direct current energy meter with direct measurement up to 1000 V / 650 A, with RS-485 interfaces for the programming software and the DC charging controller, correction of charging cable losses, operating temperature up to +80°C, certified in accordance with measuring and calibration law

## Commercial data

Item number	1269236
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CK4
Product key	CMMC31
GTIN	4063151421748
Weight per piece (including packing)	505.5 g
Weight per piece (excluding packing)	500 g
Customs tariff number	90303100
Country of origin	DE

## Technical data

### Product properties

Product type	Energy meter
Insulation characteristics	
Overvoltage category	III
Degree of pollution	2

### Electrical properties

Electric strength	3521 V (IEC 61851-23, EN 62052-31)
Supply	
Supply voltage range	19.2 V DC ... 36 V DC

### Input data

Measurement	
Input voltage range	150 V DC ... 1000 V DC
Input current range	6.5 A ... 650 A (Direct measurement)
Power consumption	< 5 W
	< 0.5 W ( $U_N$ )
	< 0.12 W ( $I_{max}$ )
Startup current $I_{st}$	0.52 A
Minimum current $I_{min}$	6.5 A
Limiting current $I_{max}$	650 A
Transient current $I_{tr}$	13 A
Reference current $I_{ref}$	130 A

### Output data

Pulse LED	1000 imp/kWh
-----------	--------------

### Connection data

Voltage	
Connection method	Screw connection
Conductor cross section rigid	0.75 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section flexible	0.75 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section AWG	20 ... 16
Tightening torque	0.5 Nm ... 0.6 Nm

### Current

Connection method	Screw connection
Screw thread	M8
	M10
Tightening torque	17.5 Nm ... 20 Nm

# EEM-PM157-SLP - Measuring device



1269236

<https://www.phoenixcontact.com/in/products/1269236>

## Interfaces

### Communication:

Communication protocol	SLIP
Communication standard	RS-485
Connection method	RJ12
Transmission speed range	9600 bps ... 115200 bps
Parity	odd, even, none

## Dimensions

Width	107.2 mm
Height	115.6 mm
Depth	66.75 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m
Max. permissible relative humidity (operation)	97.5 % (non-condensing)

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### Calibration law

Certificate	Conforms to calibration law
-------------	-----------------------------

## Standards and regulations

Standards/specifications	EN 50470-1
	EN 50470-3
	IEC 62052-41
	DIN EN 62052-11
	VDE-AR-E 2418-3-100
	EN 62053-41
	OCMF 1.0
	PTB-A 20.1
	PTB-A 50.7

## Mounting

Mounting type	NS 35 ...
Mounting position	Horizontal DIN rail

# EEM-PM157-SLP - Measuring device



1269236

<https://www.phoenixcontact.com/in/products/1269236>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1269236>

### **PTB-BG**

Approval ID: DE-23-M-PTB-0021

# EEM-PM157-SLP - Measuring device



1269236

<https://www.phoenixcontact.com/in/products/1269236>

## Classifications

### ECLASS

ECLASS-11.0	27142330
ECLASS-12.0	27142330
ECLASS-13.0	27142330

### ETIM

ETIM 9.0	EC002301
----------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1957fd60-0c59-4233-a22e-74f113e41f68

# EEM-PM157-SLP - Measuring device

1269236

<https://www.phoenixcontact.com/in/products/1269236>



## Accessories

### EEM-RS485-PCM - Programming adapter

1551889

<https://www.phoenixcontact.com/in/products/1551889>

RS-485 USB communication adapter for reading and configuring DC energy meters



---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)