

40Vmax Impact Wrench XGT®

TW011G

3/4", 1 500 Nm, 0 – 1 800 min⁻¹

Model TW011G is an Impact Wrench, High power, equipped with a long anvil and powered by a 40Vmax XGT® Li-Ion battery.

Main feature and benefits: Tip shape: Long anvil with 19mm (3/4") Square drive. Style of socket retention: C ring (with a hole). Electronic 4-stage impact power selection. Constant speed control.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	0 - 500 / 700 / 1100 / 1800 min ⁻¹
Max Fastening Torque Impact Drill	50 / 150 / 450 / 1500 Nm
Nut-busting torque	1900 Nm
Tightening Capacity Standard Bolt	M12 - M36
Tightening Capacity High Tensile Bolt	M10 - M27
Impacts per Minute (IPM)	0 - 1400 / 2000 / 2600 min ⁻¹
Drive Square	3/4 "
Sound Power Level (L _{WA})	112 dB(A)
Sound Pressure Level (L _{pA})	104 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electronic 4 stage impact power selection for added versatility
- Brushless maintenance-free and long-life motor
- Ergonomic soft grip handle provides increased comfort

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing