

EM-PSAFE-GATEWAY-IFS - Data interface



1188207

<https://www.phoenixcontact.com/in/products/1188207>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Gateway for the connection of up to 15 Interface system devices to a higher-level safe controller via PROFIsafe. The system devices are connected to the gateway via DIN rail connectors. The DIN rail connectors are provided.

Commercial data

Item number	1188207
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK7711
GTIN	4063151231675
Weight per piece (including packing)	299.7 g
Weight per piece (excluding packing)	257 g
Country of origin	DE

Technical data

Product properties

Product type	Gateways/Proxies
Insulation characteristics	
Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
Insulation characteristics	
Overvoltage category	III
Pollution degree	2

Electrical properties

Supply

Nominal supply voltage	24 V DC
Current consumption	67 mA (without connected sensors)
Fuse	≤ 8 A (external) Slow-blow

Supply

Nominal supply voltage	24 V DC
Current consumption	52 mA (without actuators connected)
Fuse	≤ 8 A (external) Slow-blow

Input data

Digital

Rated actuating voltage U_C	24 V DC $\pm 20\%$
Rated actuating current I_C	3 mA
Protective circuit	Reverse polarity protection

Output data

Digital: Switching outputs

Residual voltage	1 V
Maximum switching voltage	23 V DC ($U_B - U_{\text{resid.}}$ of the output)
Max. switching current	500 mA (per output)
Protective circuit	Reverse polarity protection

Digital: Safe digital outputs

Rated output voltage U_{SO}	24 V DC (from safe U_{SO})
Protective circuit	Overload protection
	Short-circuit protection

Connection data

Supply

Connection method	Screw connection
-------------------	------------------

EM-PSAFE-GATEWAY-IFS - Data interface



1188207

<https://www.phoenixcontact.com/in/products/1188207>

Stripping length	8 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 2 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Programming connection

Connection method	S-PORT (socket)
Number of connections	1
Number of positions	12

INTERFACE system

Connection method	DIN rail bus connectors
Number of connections	1
Number of positions	5

PROFINET (PROFIsafe)

Connection method	RJ45
Number of connections	2

Interfaces

Data: Network interface

Communication protocol	PROFINET
Connection method	RJ45 jack
Number of connections	2
Note	PROFIsafe tunneled
Transmission speed	10 Mbps
	100 Mbps

Data: Service interface

Communication protocol	Interface-System
Connection method	S-PORT (socket)
Number of connections	1
Number of positions	12

Data: Device bus

Communication protocol	Interface-System
Connection method	DIN rail bus connectors
Number of connections	1
Number of positions	5
Transmission speed	76.8 kbps

Dimensions

Width	45 mm
Height	107.8 mm
Depth	113.8 mm

Material specifications

Color	gray (RAL 7042)
Housing material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 ()
Ambient temperature (operation)	-35 °C ... 50 °C
Ambient temperature (storage/transport)	-35 °C ... 80 °C
Altitude	≤ 3000 m
Permissible humidity (storage/transport)	75 % (non-condensing)
Air pressure (operation)	70 kPa ... 108 kPa
Air pressure (storage/transport)	66 kPa ... 108 kPa (≤ 3500 m)

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Noise immunity	EN 61000-6-2

Electrostatic discharge

Standards/regulations	IEC/EN 61000-4-2
-----------------------	------------------

Electrostatic discharge

Contact discharge	6 kV
Discharge in air	8 kV
Comments	Criterion A

Electromagnetic HF field

Standards/regulations	IEC/EN 61000-4-3
-----------------------	------------------

Electromagnetic HF field

Test field strength	10 V/m
Comments	Criterion A

Fast transients (burst)

Standards/regulations	IEC/EN 61000-4-4
-----------------------	------------------

Fast transients (burst)

Signal	2 kV (test voltage)
Comments	Criterion A

Surge current load (surge)

Standards/regulations	IEC/EN 61000-4-5
-----------------------	------------------

1188207

<https://www.phoenixcontact.com/in/products/1188207>

Surge current load (surge)

Signal	1 kV ()
	2 kV ()
Comments	Criterion A

Conducted interference

Standards/regulations	IEC/EN 61000-4-6
-----------------------	------------------

Conducted interference

Comments	Criterion A
Voltage	10 V (test voltage)

Emitted interference

Standards/regulations	EN 55011
Comments	Class A, industrial applications

Standards and regulations

Standards/regulations	EN 61131-2
	EN ISO 13849-1
	IEC 61508
	IEC 62061

Air clearances and creepage distances


Standards/regulations	IEC 60664-1
-----------------------	-------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Drawings

Circuit diagram



1188207

<https://www.phoenixcontact.com/in/products/1188207>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1188207>

PROFINET

Approval ID: Z13651

PROFIsafe

Approval ID: Z20349

1188207

<https://www.phoenixcontact.com/in/products/1188207>

Classifications

ECLASS

ECLASS-11.0	27242608
ECLASS-12.0	27242608
ECLASS-13.0	27242608

ETIM

ETIM 9.0	EC001604
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)