


ITX 19 L

SCREWDRIVER BIT SOCKET 1/2" for recessed TORX® head screws, long pattern

- ▶ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ▶ Hand-operated, knurled grip
- ▶ Chrome-plated
- ▶ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ▶ TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12.5

1/2"



Code	No.	Φ	□ mm	★ mm	L ₁	L ₂	d	↺	⊞	£
6188020	ITX 19 L T20-100	T20	M4 - M5	3.86	100	62	22.5	95	5	
6188100	ITX 19 L T25-100	T25	M4,5 - M5	4.43	100	62	22.5	95	5	
6188370	ITX 19 L T27-100	T27	M4,5 - M6	4.99	100	62	22.5	96	5	
6152500	ITX 19 L T30-100	T30	M6 - M7	5.52	100	62	22.5	96	10	
6152690	ITX 19 L T40-100	T40	M7 - M8	6.65	100	62	22.5	96	10	
6155870	ITX 19 L T45-100	T45	M8 - M10	7.82	100	62	22.5	98	10	
6158700	ITX 19 L T50-100	T50	M10	8.83	100	62	22.5	124	10	
6159940	ITX 19 L T55-100	T55	M12	11.22	100	62	23.0	151	10	
6188450	ITX 19 L T60-100	T60	M14	13.25	100	60	24.7	197	5	
6105180	ITX 19 L T70-100	T70	M16	15.55	100	60	28.0	277	5	

ITX 19 B

SCREWDRIVER BIT SOCKET 1/2" for recessed TORX® head screws with pilot

- ▶ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ▶ Hand-operated, knurled grip
- ▶ Chrome-plated
- ▶ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ▶ TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12.5

1/2"



Code	No.	Φ	□ mm	★ mm	L ₁	L ₂	d	Bore	↺	⊞	£
6192720	ITX 19 B T20	T20	M4 - M5	3.86	55	17	22.5	1,55 x 1,86	75	5	
6195660	ITX 19 B T25	T25	M4,5 - M5	4.43	55	17	22.5	1,93 x 2,04	75	5	
6196390	ITX 19 B T27	T27	M4,5 - M6	4.99	55	17	22.5	2,18 x 2,29	76	5	
6200170	ITX 19 B T30	T30	M6 - M7	5.52	55	17	22.5	2,56 x 2,92	76	5	
6200410	ITX 19 B T40	T40	M7 - M8	6.65	55	17	22.5	2,92 x 3,28	91	5	
6200840	ITX 19 B T45	T45	M8 - M10	7.82	55	17	22.5	3,45 x 3,68	92	5	
6201300	ITX 19 B T50	T50	M10	8.83	55	17	23.0	3,83 x 3,78	105	5	
6202700	ITX 19 B T55	T55	M12	11.22	55	15	24.7	4,85 x 4,79	133	5	
6203270	ITX 19 B T60	T60	M14	13.25	56	16	28.0	5,63 x 7,87	182	5	


IS 19

SCREWDRIVER BIT SOCKET 1/2" for slotted head screws

- ▶ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ▶ Hand-operated, knurled grip
- ▶ Chrome-plated
- ▶ With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- ▶ Blade as per DIN ISO 2380-1, Form B

12.5

1/2"



Code	No.	mm _±	mm _±	L ₁	L ₂	d	↺	⊞	£
6161760	IS 19 6,5x1,2	1.2	6.5	60	22	22.5	71	10	
6656060	IS 19 8x1,2	1.2	8.0	60	22	22.5	80	5	
6656140	IS 19 10x1,6	1.6	10.0	60	22	22.5	115	5	
6656220	IS 19 12x2	2.0	12.0	60	22	23.0	110	5	
6162140	IS 19 14x2,5	2.5	14.0	60	20	24.7	138	5	
6656490	IS 19 16x2,5	2.5	16.0	60	20	28.0	190	5	
6656570	IS 19 18x2,5	2.5	18.0	60	20	27.0	193	10	


IKS 19

SCREWDRIVER BIT SOCKET 1/2" for cross-slotted head screws PH

- ▶ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ▶ Hand-operated, knurled grip
- ▶ Chrome-plated
- ▶ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ▶ Tip as per DIN ISO 8764-1 PH

12.5

1/2"



Code	No.	Φ PH	L ₁	L ₂	d	↺	⊞	£
6656650	IKS 19 2	2	60	22	22.5	77	10	
6656730	IKS 19 3	3	60	22	22.5	92	10	
6656810	IKS 19 4	4	60	22	23.0	106	10	


IKS 19 PZD

SCREWDRIVER BIT SOCKET 1/2" for cross-slotted head screws PZ

- ▶ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ▶ Hand-operated, knurled grip
- ▶ Chrome-plated
- ▶ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ▶ Tip as per DIN ISO 8764-1 PZ

12.5

1/2"



Code	No.	Φ PZ	L ₁	L ₂	d	↺	⊞	£
6156680	IKS 19 PZD 2	2	60	22	22.5	77	10	
6156760	IKS 19 PZD 3	3	60	22	22.5	91	10	
6156840	IKS 19 PZD 4	4	60	22	23.0	108	5	


IN 19

SCREWDRIVER BIT SOCKET 1/2" for in-hex screws

- ▶ Acc. to DIN 7422
- ▶ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ▶ Hand-operated, knurled grip
- ▶ Chrome-plated
- ▶ With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- ▶ **IN 19 17** for oil filter and drain plug screws
- ▶ * not standardised

12.5

1/2"



mm

Code	No.	*	mm	L ₁	L ₂	d	↺	⊞	£
6153070	IN 19 4	*	4	60	22	22.5	68	10	
6153150	IN 19 5	*	5	60	22	22.5	69	10	
6153230	IN 19 6	*	6	60	22	22.5	70	10	
6153310	IN 19 7	*	7	60	22	22.5	75	10	
6153580	IN 19 8	*	8	60	22	22.5	82	10	
6153660	IN 19 9	*	9	60	22	22.5	91	10	
6153740	IN 19 10	*	10	60	22	22.5	99	10	
6153820	IN 19 12	*	12	60	22	23.0	113	10	
6153900	IN 19 14	*	14	60	20	24.7	149	10	
6154040	IN 19 17	*	17	60	20	28.0	210	10	
6154120	IN 19 19	*	19	60	20	27.0	222	10	