



Connectors > PCB Connectors > Backplane Connectors > High Speed Connectors



Connector System: **Board-to-Board**

Number of Positions: **90**

Row-to-Row Spacing: **1.6 mm [.06 in]**

Mating Alignment: **Without**

Number of Rows: **6**

Features

Product Type Features

Connector System	Board-to-Board
PCB Connector Assembly Type	PCB Mount Receptacle
Shroud Style	Unshrouded
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	90
Number of Rows	6
Number of Columns	10
Backplane Architecture	Traditional Backplane
PCB Mount Orientation	Vertical
Guide Location	Center

Contact Features

Contact Current Rating (Max)	1.5 A
------------------------------	-------

Mechanical Attachment

Mating Alignment	Without
Connector Mounting Type	Panel Mount

Housing Features

Number of Shrouded Sides	0
--------------------------	---



Centerline (Pitch)	.08 mm[1.9 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	1.6 mm[.06 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in plating in component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #770969-2
06P MINI UMNL R/A HDR ASSY AU

TE Part #640310-3
UMNL SOK 12-10 PTPPHBZ

TE Part #58530-1
AMP PRO-CRIMPER HAND TOOL II

TE Part #90548-1
ASSY PRO-CRIMPER UNIV M-N-L

TE Part #90759-2
PROCRIMP DIE MINI UNIV MNL

TE Part #90760-1
PROCRIMP TL W/DIE MIN UNIV MNL

TE Part #HPP816E056
TRICAN 24V HTD2800P1B11C6STD

TE Part #770968-1
04P MINI UMNL R/A HDR ASSY SN

TE Part #184022-1
2 POS. PLUG ASSY, KEY M, BLACK

TE Part #1719183-2
8POS MQS REC COD B

Documents

Product Drawings

Fortis Zd 3Pr 10Col Vert Full Shrd Assy

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2102157-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2102157-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2102157-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Fortis Zd LRM

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English