



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Natural**

Primary Product Material: **Nylon**

Number of Positions: **15**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Configuration Features

Number of Positions	15
---------------------	----

Body Features

Primary Product Color	Natural
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]

Packaging Features

Packaging Method	Package
Packaging Quantity	1



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 350765-4
15P UMNL HDR ASSY PC



TE Part # 350434-4
15P UMNL PIN HDR ASSY NATL LF



TE Part # 350837-4
15P UMNL HDR ASSY PC LF




TE Part # 350738-1
15P UMNL PIN HDR ASSY 94VO



 TE Part # 350765-5 15P UMNL HDR ASSY PC LF	 TE Part # 350738-4 15P UMNL PIN HDR ASSY 94VO LF	 TE Part # 643429-1 15P UMNL HDR ASSY POL	 TE Part # 350736-1 15P UMNL PLUG HSG
 TE Part # 350434-1 15P UMNL PIN HDR ASSY NATL	 TE Part # 350830-1 15P UMNL HDR ASSY PC 94VO	 TE Part # 641975-1 15P UMNL PIN HDR ASSY POL NATL	 TE Part # 641976-4 15P UMNL PIN HDR ASSY POL LF
 TE Part # 1-480710-0 15P UMNL PLUG HSG NATL	 TE Part # 350714-1 15P UMNL PIN HDR ASSY 94VO	 TE Part # 350714-4 15P UMNL PIN HDR ASSY 94VO LF	 TE Part # 350992-4 15P UMNL HDR ASSY LNG/TL
 TE Part # 350837-1 15P UMNL HDR ASSY PC	 TE Part # 643430-1 15P UMNL HDR ASSY POL 94VO	 TE Part # 641976-1 15P UMNL PIN HDR ASSY POL 94VO	 TE Part # 350784-1 15P UMNL CAP HSG

Also in the Series | Universal MATE-N-LOK

 Circular Power Connectors(2)	 Connector Contacts(208)	 Connector Hardware(12)	 Power Contacts(208)
---	---	---	--



Rectangular Power Connectors(651)



Standard Circular Connectors(1)


Customers Also Bought



TE Part #212609-1
RECEPT HSG,4 POSN,METRIMATE



TE Part #60764-2
250 FASTON FLAG REC 18-14 AWG TPBR



TE Part #41495
SPADE .190(4.82 MM)12-10 AWG TPBR



TE Part #794831-1
MINI UMNL SKT SN 22-18 AWG




TE Part #350538-1
UMNL PIN 20-14 .0126 PTPBR



TE Part #2-240651-0
BLADE, SLUG




TE Part #207397-1
HSG,RECEPT 10 POSN,METRIMATE



TE Part #41473
SPADE TERMINAL 18-14 AWG TPBR



TE Part #F18659-000
HX-SCE-1K-3.2-50-4



TE Part #794413-1
03P .156 MNL CAP HSG

Documents

Product Drawings

15P UMNL STR/REL & INSRT NATL

English

CAD Files

Customer View Model

ENG_CVM_1-640724-0_B.3d_igs.zip

English

Customer View Model



[ENG_CVM_1-640724-0_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-640724-0_B.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-640724-0_S.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-640724-0_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-640724-0_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English