



Chemical protection

FLUOTECH 468

continuous wear

Tactile sensitivity with wear-indicator



CHEMICAL PROTECTION
TYPE A

EN388



3102X

EN ISO 374-1



TYPE A
ADEFGJLMNO

EN ISO 374-5



CATEGORY 3

DEXTERITY

EN420:
5/5



0334

SPECIFIC ADVANTAGES



Comfort

- Excellent flexibility and thickness optimization, due to the Mapa multi-layer technology: good dexterity and comfort



Durability

- Nitrile inner layer: excellent mechanical resistance and a longer service life



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Practical

- Green inner layer: wear-indicator for greater user safety

INDUSTRIES

- Mechanical industry
- Chemical industry
- Other industries

APPLICATIONS

- Metal degreasing and etching
- Chemical treatments (solvents)
- Galvanoplasty
- Handling and transporting chemicals (solvents)
- Manufacturing paints and varnishes
- Resin and adhesive manufacturing
- Petrochemical refining
- Printing
- Site pollution control



Chemical protection

FLUOTECH 468

continous wear

LEGENDS

EN388



MECHANICAL HAZARDS

PERFORMANCE LEVELS (X = NOT TESTED)

3	1	0	2	X	
0-4	0-5	0-4	0-4	A-F	P

Impact protection (optional)

Cut resistance according to ISO 13997

Puncture resistance

Tear resistance

Blade cut resistance

Abrasion resistance

EN ISO 374-1



CHEMICAL RISKS

A: Methanol
D: Dichloromethane
E: Carbon Disulfide
F: Toluene
G: Diethylamine
J: n-Heptane
L: Sulphuric acid 96%
M: Nitric acid 65%
N: Acetic acid 99%
O: Ammonia 25%

TYPE A

EN ISO 374-5



MICRO-ORGANISMS

Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Chlorinated
Exterior finish	Smooth
Material	Fluoroelastomer
Cuff characteristic	Feston Cuff
Colour.s	Black
Length (cm)	30
Thickness (mm)	0.51
European sizes	8 9 10

LOGISTIC DETAILS

Packaging	1 pair/carton
-----------	---------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/01/19/0326
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France