



Image may differ from product. See technical specification for details.

GEZ 204 ES

Radial spherical plain bearing, requiring maintenance, inch sizes

Radial spherical plain bearings are designed to accommodate radial and combined radial and axial loads, and also misalignment. This specific design includes a steel/steel sliding contact surface combination. The bearings require maintenance and can be relubricated via lubrication holes and an annular groove in both rings.

- Designed for radial and combined radial and axial loads
- Suitable for heavy static, alternating or impact loads

Overview

Dimensions

Bore diameter	57.15 mm
Outside diameter	90.488 mm
Width, inner ring	50.013 mm
Width, outer ring	42.85 mm

Performance

Basic dynamic load rating	280 kN
Basic static load rating	850 kN

Properties


Sliding contact surface combination	Steel/steel, standard
Material, inner ring	Bearing steel
Material, outer ring	Bearing steel
Maintenance	Relubrication required
Radial internal clearance	CN
Sealing	Without
Relubrication feature	With

Logistics

Product net weight	1.3 kg
eClass code	23-05-01-06
UNSPSC code	31171515

Technical specification


Maintenance	Relubrication required
Sliding contact surface combination	Steel/steel, standard
Material, inner ring	Bearing steel
Material, outer ring	Bearing steel
Sealing	Without



Dimensions

d	57.15 mm	Bore diameter
D	90.488 mm	Outside diameter
B	50.013 mm	Width
C	42.85 mm	Width outer ring
α	6 °	Angle of tilt
d_k	82.169 mm	Raceway diameter inner ring
b	5.6 mm	Width annular lubrication groove at outer ring
b_1	5 mm	Width annular lubrication groove at inner ring

M	4 mm	Diameter lubrication hole (outer ring)
r ₁	min. 0.6 mm	Chamfer dimension bore
r ₂	min. 1 mm	Chamfer dimension outer ring



Abutment dimensions

d _a	min. 61.7 mm	Abutment diameter shaft
d _a	max. 65.2 mm	Abutment diameter shaft
D _a	min. 78.1 mm	Abutment diameter housing
D _a	max. 85.3 mm	Abutment diameter housing
r _a	max. 0.6 mm	Fillet radius shaft
r _b	max. 1 mm	Fillet radius housing

Calculation data

Basic dynamic load rating	C	280 kN
Basic static load rating	C ₀	850 kN
Specific dynamic load factor	K	100 N/mm ²
Specific static load factor	K ₀	300 N/mm ²

Material constant	K_M	330
-------------------	-------	-----

Tolerances and clearances

- [General bearing specifications](#)

RADIAL LOCATION OF BEARINGS

- [Recommended fits](#)

More Information

 Product details Radial spherical plain bearings requiring maintenance Maintenance-free radial spherical plain bearings General bearing specifications Temperature limits	 Engineering information Principles of selection	 Tools SKF Product select Heater selection tool
--	--	--



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.