

WORKSHOP LAYOUT



250 KG

Mobile pedestals

Door and 4-drawer unit

Resistant and durable, they are designed for intensive use and can be locked.

- Top plate in sheet metal with 30 mm lip to prevent tools from falling.
- Extra-thick, non-slip, ribbed rubber mat to reduce noise pollution.
- Meticulous finish: tough, durable grey epoxy paint.
- Ø 100 mm wheels, 2 fixed + 2 swivel with brakes.
- Load capacity per drawer: 40 kg.
- Central locking system with 1 set of 2 keys.



880 008 412



880 008 413

Reference	Features	Overall dimensions (WxDxH) mm	Wheel Ø mm	Weight kg
880 008 412	1 block of 4 drawers	620 x 625 x 470	100	45
	2 drawers, height 100 mm (useful 85 mm)			
	2 drawers, 150 mm high (useful 140 mm)			
880 008 413	1 door unit with 1 shelf			25

OPTIONS



882 006 040
Partitions for drawers 100 mm high, i.e. the first 2 drawers.
6 partitions included.



882 006 037
Additional shelf for door unit. Max. 4 shelves with 9 possible positions, adjustable in 55 mm increments.

