



Product data sheet

Power tools for trade & industry

ISR 18V-30 PHX

INDUSTRIAL ISR 18V-30 PHX



Consistent, reliable & affordable 18V smart solution made for industrial assembly lines

Extended lifetime for optimal operation without part failure, industrial grade clutch endurance & switch cycles boosting screw counts
Precision clutch with auto-shutoff, in combination with special engineered gearbox enabling 2X* higher speed output consistency and torque accuracy
Slim handle, light weight & short head length to minimize operation fatigue and maximize application flexibility

The most important data

Torque (hard)	9 – 30 Nm
Speed	0 – 1,400 rpm
Auto Shutoff Torque	1.6 - 7.6 Nm

Part Number 0 601 9M7 120

Technical data

Technical data

Description

When you're fastening thousands of screws a day in an assembly line, you need a heavy-duty tool you can rely on to deliver long-term, accurate tightening and consistent performance. Our ISR 18V-30 PHX Industrial cordless drill driver offers up to twice the standard speed output consistency and torque accuracy thanks to its special engineering. Equipped with a precision clutch, this durable tool gives you significant performance outcome and extremely high production efficiency, especially in tightening applications for industrial assembly lines. The hex-head universal bit locker ensures a quick and dependable exchange of screw bits. What's more, this smart drill driver makes keeping track of tools with its embedded NFC technology for inventory

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

Torque, from (hard)	9 Nm
Torque, to (hard)	30 Nm
Torque (hard)	9 – 30 Nm
Speed, from	0 rpm
Speed, up to	1,400 rpm
Speed	0 – 1,400 rpm
Direction of rotation	R/L
Weight	0.7 kg
Bit holder	1/4" Hex Uni
Connector type	Shut-off clutch
Auto Shutoff Torque, from	1.6 Nm
Auto Shutoff Torque, to	7.6 Nm
Auto Shutoff Torque	1.6 - 7.6 Nm



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

