



Technical data


NU2312EAT2X

Single row cylindrical roller bearings

Single row cylindrical roller bearing, floating, separable, polyamide cage



ULTAGE®

VISUAL (S)



NU2312EAT2X

Single row cylindrical roller bearings




NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

NU2312EAT2X

Single row cylindrical roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	60 mm
D - External diameter	130 mm
B - Bearing/Inner ring width	46 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

NU2312EAT2X

Single row cylindrical roller bearings

PRODUCT DEFINITION

E - Upper roller diameter	115 mm
F - Under roller diameter	77 mm
d1 - IR flange outer diameter	84,6 mm
rNs - Min fillet radius	2,1 mm
rs - Min fillet radius	2,1 mm
Radial clearance class	CN
Mass	2,96 kg

PRODUCT PERFORMANCE

C - Dynamic load	263000000 mN
C0 - Static load	262000000 mN
Cu - Fatigue limit load	32000000 mN
N lim - Oil lubrication limit speed	37200 °/s
N lim - Grease lubrication limit speed	26400 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	71 mm
db min - Min inner ring GO diameter	79 mm
Da max - Max shoulder diameter OR	119 mm
Db min - Small face shoulder min diameter	117 mm
ra max - Max fillet radius	2 mm
r1a - Max fillet radius	2 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = Fr$$

Equivalent static radial load

$$P_0 = Fr$$

