

2108610-5


✓ ACTIVE

TE Internal #: 2108610-5
Preloaded - C-Clip PCB Spring Contact, Scalable, Side Protected,
1.4 mm [.055 in] Uncompressed Height, 2.9 mm [.114 in] Length, 1
mm [.039 in] Width

[View on TE.com >](#)



Connectors > Contacts > PCB Spring Contacts



Spring Finger Type: **Preloaded - C-Clip**
Scalable: **Yes**
Side Protected: **Yes**
Uncompressed Height: **1.4 mm [.055 in]**
Product Length: **2.9 mm [.114 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Spring Finger Type	Preloaded - C-Clip
Scalable	Yes

Configuration Features

Number of Positions	1
Side Protected	Yes

Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold
Contact Working Range (Low)	.8 mm[.031 in]
Contact Working Range (High)	1 mm[.039 in]
Point of Contact Area Plating Material	Gold



Contact Current Rating (Max)	.5 A
------------------------------	------

Dimensions

Uncompressed Height	1.4 mm[.055 in]
Product Length	2.9 mm[.114 in]
Product Width	1 mm[.039 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	9000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2108613-5
2.4H SPRING FINGER WITH EMBOSS

Customers Also Bought

TE Part #1-1462037-8
IM03TS=IM RELAY 140mW 5V

TE Part #5-1625885-6
1W SM M/OX 5% 2R7

TE Part #8-5353164-6
ON TAPING (EMBOSS) 0.5MM PITCH
FS CONN.

TE Part #2-2176592-2
RLC73PD 2E 1R0 1% 1K RL

TE Part #5-1625885-5
1W SM M/OX 5% 2R2

TE Part #2301844-1
AMPL REC HD20, R/A, 9P, B/L, 4-40 INS

TE Part #5-2176337-3
CRGCO 0402 220K 1%

TE Part #3-826646-2
32P AMPMODU II STIFT LEI

TE Part #EEC-5X650B
ENCLOSURE, 5 X 6.50, BLK, NO VENT

TE Part #1649329-4
RTE24012

Documents

Product Drawings

1.4H SPRING FINGER WITH EMBOSS

English

CAD Files

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_2108610-5_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108610-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108610-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English