
solenoid valve **VUVG-B14-B52-ZT-F-1T1L** Part number: 573484





Data sheet

Feature	Value
Valve function	5/2 bistable
Type of actuation	electrical
Valve size	14 mm
Standard nominal flow rate	510 l/min
Operating pressure	-0.9 10 bar
Design structure	Piston slide
Protection class	IP65
	IP67
Authorisation	c CSA us (OL)
	c UL us - Recognized (OL)
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Manual override	detenting
	Pushing
Type of piloting	Piloted
Pilot air supply	external
Flow direction	reversible
Signal status display	LED
Pilot pressure	1.5 8 bar
Max. switching frequency	3 Hz
Switching time reversal	9 ms
Duty cycle	100%
Max. positive test pulse with logic 0	1,600 μs
Max. negative test pulse with logic 1	3,000 μs
Characteristic coil data	22 V DC: 1 W
Permissible voltage fluctuation	+/- 10 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Vibration resistance	Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-5 60 °C
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-5 60 °C
Product weight	98 g
Electrical connection	via manifold block
Mounting type	on manifold rail
Materials note	Conforms to RoHS
Material seals	HNBR
	NBR
Material housing	Wrought Aluminium alloy