

500 SETS PER INNER
CARTON BOX
P/N: 89499-9027



FORMAT: TC-4b-prod-G
REVISION: B

MATERIALS AND FINISHES:



BODY BRASS
PLATED GOLD

CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON



MMCX JACK
INTERFACE




FOR PCB LAYOUT SEE SHEET 4

REEL SIZE FOR TAPE AND REEL: 1500 PIECES

		73415-0969	PER COMMERCIAL REQUIREMENTS	ONE PIECE PER BAG OF 73415-0961
		73415-0968	PER COMMERCIAL REQUIREMENTS	INDIVIDUAL BAGS -- SEE SHEET 2
		73415-0967	PER MILITARY REQUIREMENTS	LEADS ORIENTED OPPOSITE FEED HOLES WITHOUT LABEL
		73415-0966	PER COMMERCIAL REQUIREMENTS	LEADS ORIENTED TOWARDS FEED HOLES WITHOUT LABEL
		73415-0965	PER COMMERCIAL REQUIREMENTS	LEADS ORIENTED OPPOSITE FEED HOLES
		73415-0964	PER MILITARY REQUIREMENTS	LEADS ORIENTED TOWARDS FEED HOLES
		73415-0963	PER COMMERCIAL REQUIREMENTS	LEADS ORIENTED TOWARDS FEED HOLES
		73415-0962	PER MILITARY REQUIREMENTS	LEADS ORIENTED OPPOSITE FEED HOLES
CECC-22-340	INTERFACE	73415-0961	PER COMMERCIAL REQUIREMENTS	TRAY PACK
PS-89675-1920	ELECTRO/MECH PERFORMANCE	73415-0960	PER MILITARY REQUIREMENTS	TRAY PACK
SPECIFICATION	DESCRIPTION	PART NUMBER	GOLD PLATING	PACKAGING

CHG: ADD -0969 PACKING FOR -0960/0961 WAS SINGLE BAGS EC NO: URF2012-0471 2012/02/10 DRWN:JWIENER CHKD:SSS 2012/02/10 APPR:JWIENER 2012/02/10 REV		DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± 2 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
					DRAWN BY EDC	DATE 1999/02/15	TITLE MMCX JACK PCB EDGE MOUNT 50 OHM MMCX-J/PCB				
					CHECKED BY DHG	DATE 1999/02/15					
					APPROVED BY JWIENER	DATE 2010/02/24	MOLEX MOLEX INCORPORATED				
					MATERIAL NO.	DOCUMENT NO.			SHEET NO.		
					SEE TABLE	SD-73415-096			1 OF 4		
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

13 12 11 10 9 8 7 6 5 4 3 2 1



NOTE:

1. DIMENSIONS ARE PROVIDED FOR REFERENCE ONLY.

PART # 73415-0962/73415-065/73415-0967

PACKAGING FOR 73415-0968 ONLY
(INDIVIDUAL BAGS):

1. PASTE COLOR LABEL OFFERED BY CUSTOMER
ON EVERY POLYBAG SHOWING QTY, CUSTOMER
P/N:- K00G0027

2. PASTE COLOR LABLE ON MASTER CARTON
SHOWING P/N & QTY.

CHG: SEE SHEET 1

EC NO: URF2012-0471

DRWN:JWIENER 2012/02/10

CHKD:SSS 2012/02/10

APPR:JWIENER 2012/02/10

REV

DESCRIPTION

QUALITY SYMBOLS

▽=0

▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
EDC	1999/02/15
CHECKED BY	DATE
DHG	1999/02/15
APPROVED BY	DATE
JWIENER	2010/02/24

MATERIAL NO.

SEE SHEET 1

SCALE

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE

MMCX JACK PCB EDGE MOUNT

50 OHM

MMCX-J/PCB


MOLEX INCORPORATED

DOCUMENT NO.

SD-73415-096



SHEET NO.

2 OF 4



SECTION D-D

MOLEX P/N: 73415-0961
1500 PLACES




SECTION C-C

NOTES:

1. DIMENSIONS ARE PROVIDED FOR REFERENCE ONLY.

PART # 73415-0963/73415-0964/73415-0966

CHG: SEE SHEET 1 EC NO: URF2012-0471 DRWN: JWIENER CHKD: SSS APPR: JWIENER F5	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY	DATE	TITLE		
			4 PLACES	± ---	± ---	EDC	1999/02/15	MMCX JACK PCB EDGE MOUNT 50 OHM MMCX-J/PCB		
			3 PLACES	± ---	± ---	CHECKED BY	DATE			
			2 PLACES	± ---	± ---	DHG	1999/02/15			
			1 PLACE	± ---	± ---	APPROVED BY	DATE			
			ANGULAR ± 2 °		JWIENER	2010/02/24	 MOLEX INCORPORATED			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.			DOCUMENT NO.		SHEET NO.
					SEE SHEET 1			SD-73415-096		3 OF 4
					SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



C	0.80 MM / .031 INCHES	.039 REF	1.00 REF	-----	-----	.055 REF	1.40 REF	.043 REF	1.10 REF	.071 REF	1.80 REF
	1.00 MM / .039 INCHES	.035 REF	0.90 REF	.012 REF	0.30 REF	.071 REF	1.80 REF	.047 REF	1.20 REF	.065 REF	1.64 REF
	1.60 MM / .063 INCHES	.016 REF	0.40 REF	.063 REF	1.60 REF	.110 REF	2.80 REF	.091 REF	2.30 REF	.059 REF	1.50 REF
	PCB THICKNESS	IN	MM	IN	MM	IN	MM	IN	MM	IN	MM
B	A		B			C		D		E	
	CHG: SEE SHEET 1 EC NO: URF2012-0471 2012/02/10 DRAWN: JWIENER CHKD: SSS 2012/02/10 APPR: JWIENER 2012/02/10 REV				QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± 2 °		DIMENSION STYLE MM/IN DRAWN BY DATE EDC 1999/02/15 CHECKED BY DATE DHG 1999/02/15 APPROVED BY DATE JWIENER 2010/02/24		SCALE DESIGN UNITS METRIC THIRD ANGLE PROJECTION	
A	F5				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE SHEET 1		DOCUMENT NO. SD-73415-096		SHEET NO. 4 OF 4