



### Contact characteristics

IEC Conventional free air thermal current $I_{th} \leq 40^\circ\text{C}$	A	1000
Rated insulation voltage $U_i$ IEC/EN	V	1000
Rated impulse withstand voltage $U_{imp}$	kV	12
Operating current $I_e$		
AC21A		
	400V	A 1000
	500V	A 1000
	690V	A 1000
	1000V	A 1000
AC22A		
	400V	A 1000
	500V	A 1000
	690V	A 800
AC23A		
	400V	A 1000
	500V	A 1000
	690V	A 800
	1000V	A 400
Power dissipation per pole max	W	63
Rated operational power AC23A		
	400V	kW 560
	690V	kW 800
Reactive power for control of capacitors at		
Rated short time current (1s) $I_{cw}$ (rms)	kA	20
Conditional short-circuit current (rms)	kA	50
Short-circuit protection with fuse	Class/A	gG/1000
Making capacity AC23A 400V	A	10000
Breaking capacity AC23A 400V	A	8000
Mechanical life	cycles	5000

### Mechanical features

Operating position	normal allowable	Vertical plan Any
Fixing		Screw
Terminals	type	M12 x 40
Tightening torque for terminals	min	Nm 50
	max	Nm 75
	min	lbin 442
	max	lbin 664
Conductor section	IEC min	mm <sup>2</sup> 2x300
	AWG/kcmil min	2x600

AWG/kcmil max    kcmil    4x600

**Ambient conditions**

Operating temperature

min	°C	-25
max	°C	+55


Storage temperature

min	°C	-40
max	°C	+70


Max altitude

m	3000
---	------

**Dimensions**



**Wiring diagrams**



**Certifications and compliance**

**Compliance**

IEC/EN 60947-1  
IEC/EN 60947-3

---

ETIM classification

ETIM 8.0

EC000216 -  
Switch  
disconnector