






SPECIFICATIONS		MALE END VIEW	FEMALE END VIEW	REV	CHG	DATE	DESCRIPTION	REVISION
HOUSING MATERIAL/COLOR	NYLON/BLACK	 <p>Type of coding</p>	 <p>J1~J4 Type of coding</p>					
CONTACT CARRIER MATERIAL/COLOR	TPU/BLACK							
RECEPTACLE MATERIAL / PLATING	BRASS/NICKEL							
CONTACT MATERIAL / PLATING	BRASS/GOLD							
O-RING MATERIAL	FPM/FKM							
OPERATING CURRENT [A]	2A PEG SIGNAL, 9A TOTAL							
OPERATING VOLTAGE [V]	10~30 VDC							
OPERATING TEMPERATURE	-25°C~+85°C							
PROTECTION CLASS	IEC IP67							
POTTING MATERIAL	POLYURETHANE(PU)							



PROCESS BY		DATE		 <p>Technology in connectors™</p>
CHECKED BY		DATE		
DRAWING BY	Lillian	DATE	25/06/26	
DIMENSIONS NOT SPECIFIED ARE IN MILLIMETERS				1st Angle Projection 
DESCRIPTION:				
SAL-12-4FK5-23-1FS12				
PART NO.				43-08001
REV	A	SHEET	1 OF 1	