




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Cable-to-Board**
Number of Positions: **80**
Centerline (Pitch): **1.27 mm [.05 in]**
Row-to-Row Spacing: **1.27 mm [.05 in]**
Number of Rows: **2**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	80
Number of Rows	2

Electrical Characteristics

Operating Voltage	30 VAC
Insulation Resistance	5000 MΩ

Body Features

Mating Retention Feature Material	Stainless Steel
Primary Product Color	Black
Connector Profile	Standard



Contact Features

Contact Underplating Material	Nickel
Mating Pin Diameter	.46 mm[.018 in]
Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
Wire Contact Termination Area Plating Material	Tin
Contact Layout	Matrix
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
Wire Contact Termination Area Plating Thickness	1.27 μm[50 μin]
Contact Type	Receptacle
Contact Current Rating (Max)	.5 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Connector Width	8.31 mm[.327 in]
Wire Size	28 AWG
Connector Height	17.56 mm[.691 in]
Connector Length	59.13 mm[2.328 in]
Row-to-Row Spacing	1.27 mm[.05 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------



Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Quantity	8
Packaging Method	Tube

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-147384-8
80 50/50 GRID SMT RCPT VC LF




TE Part # 5-104652-8
80 50/50 GRID DRST SFMNT RCPT



TE Part # 843477-1
TOOL, EXTRACTION RESET

Also in the Series | AMPMODU 50/50 Grid




Board-to-Board Headers & Receptacles(193)



Connector Caps & Covers(7)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(193)



Rectangular Power Connectors(12)



Ribbon Cable Connectors(21)

Customers Also Bought



TE Part #5-102202-1
04 MODII HDR SRST SHRD LF




TE Part #154740-E
SMCQ 12 F AB VV 7-03 CL * 0007 137 E002



TE Part #2101551-2
PLUG,40 POS,Sz105,w/SOLDER CUPS, 240 POT




TE Part #364915-E
STVC 96 M ABC VVV 4-00 0606 * * 247 E007



TE Part #1055689-1
2367 5002 54,VERT PLUG




TE Part #8-102202-4
03 MODII HDR SRST SHRD LF



TE Part #5207953-3
FEMALE SCREWLOCK, SHORT, ZN



TE Part #3-1415055-1
SR4D4024



Documents

Product Drawings

80 50/50 GRID RCPT W/LTCH LF

English

CAD Files

Customer View Model

ENG_CVM_CVM_5-104892-8_F.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-104892-8_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-104892-8_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION1AND2

English

Ribbon Cable Interconnect Solutions

English

Fine Pitch Stacking Connectors - 1.27mm AMPMODU 50/50 Grid Connectors

English

5-1773700-6_AMPMODU_50_50_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English

