
BES M12MG-USC30B-BV02 BES004T





- Non-polarized
- Normally open (NO)
- 3.00 mm
- Flush (shielded)
- Cable, PVC, 2.00 m

General attributes Approvals / Conformity

EAC Basic standard Enclosure Type per IEC 60529 Function indicator IP67 Yes Operating distance marking --Yes Polarity reversal protected Power indicator No Short circuit protected Trademark

Electrical attributes Connection type Eff. operating current le Eff. operating voltage Ue DC Electrical version Load capacitance max. (at Ue) Minimum operating current Im
Operating voltage UB max. DC [V] Operating voltage UB min. DC [V] Rated insulation voltage Ui Rated short circuit current Ripple max. (% of Ue) Switching freq. f max. (at Ue) Switching function Switching output Voltage drop static max.

cULus CE IEC 60947-5-2 GLOBAL 315 a

Cable 100 mA 24.0 V DC, direct current $1.000 \, \mu F$ 5 mA 36.0 V 10.0 V 75 VDC 100 A 15 % 1300 Hz Normally open (NO) Non-polarized 5.0 V







IND. CONT. EQ
81U2
US for use in the secondary of a class 2 source of supply
Environmental - Type 1 Enclosure



Mechanical attributes

Ambient temperature Ta max. 70 °C -25 °C Ambient temperature Ta min.
Assured operating distance Sa 2.40 mm Cable diameter D max. 4.6 mm PVC Cable jacket material Cable length 2.00 m Conductor cross-section 0.34 mm² Depth Diameter d1 43.0 mm M12x1 Eff. operating distance Sr 3.00 mm Housing material Mech. installation condition CuZn Flush (shielded) Mounting length 40.0 mm Number of conductors Rated operating distance Sn [mm] 3.00 mm PA 12 Nickel-free coating Sensing face material Surface protection Tightening torque

Remarks

Specify maximum attainable switching frequency (not per IEC 60947-5-2) Embeddable: See installation notes for inductive sensors with extended switching distance 825357.

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.

