

Order Code: TBS014




Performance Data	
Input Power (W)	28
Lumens (lm)	2500
System Efficacy (Lumens/Watt)	89
Rated Life (Hours)	30000
Colour Temperature (K)	4000
Colour Rendering (Ra)	80
Beam Angle (°)	160°

Electrical Data	
Input Voltage (V) ±10%	220-240

Safety Thermal	
Maximum Ambient Temperature (°C)	+40
Minimum Ambient Temperature (°C)	-20

Physical Data	
Lens Type	Thermal Plastic
Case Material	Aluminium Substrate
Dimensions (mm)	1800mm (T8) G13
Weight (kg)	0.330kg
IP Rating	IP20



Notes:

This Product Specification contains data about typical performance at nominal power. Actual values may depend on ballast and applications. Complies with (CE), Low Voltage (CE), WEEE and RoHSDirective.

Data is based upon tests performed by Venture Lighting in a controlled environment and is representative of relative performance at the relevant nominal power/voltage (e.g. 110/240/415). Actual performance can vary depending on operating conditions.

Data is subject to change without notice.