



AMP-LATCH | AMP-LATCH Universal Headers

TE Internal #: 5102160-3
Wire-to-Board, 16 Position, 2.54 mm [.1 in] Centerline, Right Angle,
Through Hole - Solder, AMP-LATCH Universal Headers, Ribbon
Cable Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors >
AMP-LATCH UNIVERSAL HEADERS



Connector System: **Wire-to-Board**
Number of Positions: **16**
Centerline (Pitch): **2.54 mm [.1 in]**
PCB Mount Retention: **Without**
PCB Mount Orientation: **Right Angle**

[All AMP-LATCH UNIVERSAL HEADERS \(523\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Ribbon Cable Connector Header Type	Universal Ejection Pin Headers
Connector System	Wire-to-Board
Connector & Housing Type	Plug
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	16
PCB Mount Orientation	Right Angle
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
Insulation Resistance	5000 MΩ



Body Features

Primary Product Color	Black
Connector Profile	Standard

Contact Features

Contact Underplating Material	Nickel
	30 µin
Mating Square Post Dimension	.64 mm[.025 in]
Contact Shape & Form	Square
PCB Contact Termination Area Plating Material Thickness	2.54 µm[100 µin]
Contact Mating Area Plating Material	Gold (Au), Gold Flash over Palladium Nickel
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Type	Pin
Contact Current Rating (Max)	1 A

Termination Features

Termination Post & Tail Diameter	.64 mm[.025 in]
Termination Post & Tail Length	2.79 mm[.11 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	Without
Mating Alignment Type	Center, Dual Polarizing Bar
Mating Retention	With
Mating Retention Type	Ejection Latch
Connector Mounting Type	Board Mount

Housing Features

Mating Entry Location	Top
Housing Material	Nylon - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions



Shrouded End Dimension	3.81 mm[.15 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	13.94 mm[.55 in]
Connector Length	39.62 mm[1.56 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Housing Temperature Rating	High
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	70
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C






Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1658527-6 622-1630LF FEM SOCKT,LEAD FREE	 TE Part # 1-1658526-0 609-1601MLF FEM SCKT,LEAD FREE	 TE Part # 1658528-5 636-2641LF FEM SOCKT,LEAD FREE	 TE Part # 6-1437020-6 609-1631HD=FSKT IDC S 16 SR
 TE Part # 1658620-3 16 NOVO MIL 15DP, LEAD FREE	 TE Part # 1658623-3 16 NOVO MIL 30DP, LEAD FREE	 TE Part # 1658622-3 16 NOVO MIL/CTR 30DP,LEAD FREE	 TE Part # 2-1658526-9 609-1630LF=FSKT IDC S 16 30AU
 TE Part # 499252-8 016 STRAIN RELIEF A-L RCPT	 TE Part # 2-1658528-7 636-1641LSLF FEMALE SOCKET CON	 TE Part # 1-1658528-4 636-1630LF=FEM SKT BLADE POL 1	 TE Part # 1658624-3 016 NOVO DUAL 30DP FT
 TE Part # 1-1658526-1 609-1641LF FEM SOCKT,LEAD FREE	 TE Part # 1658621-3 16 NOVO MIL/CTR 15DP,LEAD FREE	 TE Part # 1658527-7 622-1641LF FEM SOCKT,LEAD FREE	

Also in the Series | AMP-LATCH Universal Headers



Connector Hardware(13)



Ribbon Cable Connectors(523)

Customers Also Bought



TE Part #AS010-35PN
RECEPT.2 HOLE MNT.TYPE 0



TE Part #1-1437624-1
PKA50B1/8=KNOB PLASTIC 1/8 SHA



TE Part #2-1437558-0
MTA206N=(MSTA) SW TOG DPDT



TE Part #5102160-6
A/L UNIV HDR 26P RA



TE Part #3-1676914-7
YR1 0.1% 47K5



TE Part #AS212-35PN
RECEPT.BOX MTG.TYPE 2



TE Part #103638-1
02 MTE HDR SRST LATCH .100CL



TE Part #103638-2
03 MTE HDR SRST LATCH .100CL



TE Part #102241-3
05 MODIV HSG COMP SR .100 POL



TE Part #102320-1
UNIVERSAL HEADER LATCH

Documents

Product Drawings

A/L UNIV HDR 16P RA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5102160-3_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5102160-3_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5102160-3_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPMODU_INTERCONNECTION_SYSTEM_SECTION5](#)

English

[Ribbon Cable Interconnect Solutions](#)

English

Product Specifications

[Product Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English