



## Pullers, two-armed

**11251**

Product no. **71025102**  
GTIN **4018754342044**  
Model **11251/2**

### Label.

Puller Clamping w.220mm x Clamping d.170mm

### Properties.

- two-armed
- with self-centring puller arms
- for gears, ball bearings, pulleys and similar parts from a shaft or axle
- double-sided use of the extractor hooks: narrow arm end (20 mm) for narrow installation spaces, wide arm end (24 mm) with slot (8 mm) for pulling off washers or gear wheels with the aid of 8 mm screws
- nitrided spindle, no lubrication required, maintenance-free
- zinc plated

## Benefits.

For quick and reliable removal of gears, ball bearings, pulleys and for extracting the outer rings of ball bearings and bushings from drilled holes.

Automatic pressure of the arms under load makes application easier.

The nitrided surface of the spindle allows it to move easily so it does not require additional lubrication.

The arm ends have a narrow and wide design and can therefore be used on both sides.

Outstanding flexural strength thanks to legs with precisely manufactured profiles and smooth, milled guides.

## Product highlights.


### For increased safety.

Thoughtfully designed, die-forged and precisely machined, hardened and tempered on state-of-the-art machines - the STAHLWILLE puller range offers numerous products for a wide range of applications. For example, terminal pullers, pullers for ball joints, counter stays or ball joint extractors - always in premium quality.



### Adapted access geometry.

Heavy-duty puller hooks made of oil-hardened Chrome Alloy Steel with special access geometry for tight spaces. Custom radii for shafts and axes.



### Reliable sliding properties.

The high-quality tempered and specially coated pressure spindle has particularly good sliding properties in the thread, is maintenance-free and does not require oiling.





**Protection against damage.**

The centering tip is freely rotating - to protect the shafts from damage.



**Sturdy design.**


High bending rigidity thanks to cross members with precisely calculated profile ribs and milled, smooth guideways.



**Flexible puller hooks.**

The two-sided puller hooks can be used flexibly because they have different designs at both ends. The narrow side (20 mm) is perfect for tight spaces, while the wide side (24 mm) has an 8 mm slot that allows effortless removal of washers or gears with 8 mm screws.

## Technical drawing.



## Technical attributes.

External hex drive (mm)	19 mm
Thickness of hook base tip mm (a)	3 mm
Hook base width mm (b)	24 mm
Hook foot depth mm (c)	12 mm
Hook width	20/24 mm
Size	2
Number of hooks	2
max. load	5 t
Clamping depth (h) mm	170 mm
Spindle thread size	M18 x 1,5 x 170
Span mm (w)	220 mm

## Logistics data.

Depth mm (IFS)	290
Width mm (IFS)	235
Height mm (IFS)	45
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	290
Width (packaged, mm)	235
Height (packaging, mm)	45
Volume (packaged, dm3)	3.06675 dm3
Product no.	71025102
Weight (gross, kg)	1,760
Weight PAP (kg)	0,006
Weight PVC (kg)	0,000
GTIN	4018754342044
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82055980
Packing standard	1
Weight (g)	2300 g

## Variants.

Product no.	Model No. (ERP)	Description	GTIN
71025101	11251/1	Puller Clamping w.160mm x Clamping d.130mm	4018754342037
71025102	11251/2	Puller Clamping w.220mm x Clamping d.170mm	4018754342044

## GTIN.



## Spare part(s), spare part(s) for.



79281007  
Puller spindle

## Images.



**STAHLWILLE Eduard Wille GmbH**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal