



GCS-035PCM-SCP DISPENSIBLE PCM

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830
Date of issue: 8/3/2017 Revision date: 2/27/2019 Version: 1.2

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture UFI Number 3CWC-9004-S00X-4D5R
Product name : GCS-035PCM-SCP DISPENSIBLE PCM
Product code : GCS-035PCM-SCP
Type of product : Thermal interface material, Fillers, putties, plasters, modelling clay

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Use of the substance/mixture : Thermal interface material
Function or use category : Conductive agents, Fillers

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Supplier

UK

RS Components Ltd
Birchington Road
Corby
Northants
NN17 9RS
Tel: +44 (0) 845 850 9900
Email: RCustomerServicesUK@rs-components.com
Website: www.rs-online.com

Ireland

RS Components Ltd
Glenview Industrial Estate
Herberton Road
Rialto
Dublin 12
Tel: +353 (0) 1 415 3100
Email: Enquiries.ie@rs-components.com
Website: www.rs-online.com

1.4. Emergency telephone number

Emergency number : +44 1865 407 333 (24hr) +44 1865 407333 (24hr)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin corrosion/irritation, Category 2 H315
Germ cell mutagenicity, Category 1B H340
Carcinogenicity, Category 1B H350
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

Causes skin irritation. Causes serious eye irritation.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

GHS08

Signal word (CLP) : Danger

GCS-035PCM-SCP DISPENSIBLE PCM

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Hazardous ingredients	: LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY; ALPHA ALUMINIUM OXIDE
Hazard statements (CLP)	: H315 - Causes skin irritation. H340 - May cause genetic defects (inhalation). H350 - May cause cancer (inhalation, oral).
Precautionary statements (CLP)	: P264 - Wash hands thoroughly after handling. P280 - Wear eye protection, protective gloves. P302+P352 - IF ON SKIN: Wash with plenty of soap and water. P308+P313 - IF exposed or concerned: Get medical advice. P332+P313 - If skin irritation occurs: Get medical advice/attention. P362+P364 - Take off contaminated clothing and wash it before reuse. P501 - Dispose of contents and container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ALPHA ALUMINIUM OXIDE	(CAS-No.) 1344-28-1 (EC-No.) 215-691-6	60	Flam. Sol. 1, H228 Skin Irrit. 2, H315
LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY	(CAS-No.) 64742-48-9 (EC-No.) 265-150-3 (EC Index-No.) 649-327-00-6	5 - 10	Muta. 1B, H340 Carc. 1B, H350 Asp. Tox. 1, H304

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water. Take off contaminated clothing. If skin irritation occurs: Get medical advice/attention.
First-aid measures after eye contact	: Rinse eyes with water as a precaution. Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Call a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact	: Irritation.
Symptoms/effects after eye contact	: Eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam.
------------------------------	----------------------------------

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire	: Toxic fumes may be released.
--	--------------------------------

5.3. Advice for firefighters

Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.
--------------------------------	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures	: Ventilate spillage area. Avoid contact with skin and eyes.
----------------------	--

6.1.2. For emergency responders

Protective equipment	: Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
----------------------	---

GCS-035PCM-SCP DISPENSIBLE PCM

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Mechanically recover the product.

Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Wear personal protective equipment.

Hygiene measures : Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY (64742-48-9)

EU	Local name	White spirit Type 3
EU	IOELV TWA (mg/m ³)	116 mg/m ³
EU	IOELV TWA (ppm)	20 ppm
EU	IOELV STEL (mg/m ³)	290 mg/m ³
EU	IOELV STEL (ppm)	50 ppm
EU	Notes	skin. (Year of adoption 2007)
EU	Regulatory reference	SCOEL Recommendations
Germany	TRGS 910 Acceptable concentration notes	

ALPHA ALUMINIUM OXIDE (1344-28-1)

Germany	TRGS 910 Acceptable concentration notes	
United Kingdom	Local name	Aluminium oxides
United Kingdom	WEL TWA (mg/m ³)	10 mg/m ³ inhalable dust 4 mg/m ³ respirable dust
United Kingdom	Regulatory reference	EH40/2005 (Third edition, 2018). HSE

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

Personal protective equipment:

Protective clothing. Safety glasses. Gloves.

Materials for protective clothing:

Condition	Material	Standard
Good resistance:	Tyvek®	EN 14387, EN 1073-2

Hand protection:

Protective gloves

Type	Material	Permeation	Thickness (mm)	Penetration	Standard
Disposable gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	0.11		EN 374-2

Eye protection:

Safety glasses

GCS-035PCM-SCP DISPENSIBLE PCM

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Type	Use	Characteristics	Standard
Safety glasses	Dust, Droplet		EN 166
Skin and body protection:			
Wear suitable protective clothing			
Type		Standard	
Disposable gloves, Disposable gowns		EN 1073-2	
Respiratory protection:			
In case of insufficient ventilation, wear suitable respiratory equipment			
Device	Filter type	Condition	Standard
Disposable half mask	Type P3		EN 140

Personal protective equipment symbol(s):



Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: white.
Odour	: Characteristic odour.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: Not applicable
Boiling point	: No data available
Flash point	: 321 °C
Auto-ignition temperature	: Not applicable
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 1.8 - 2.5
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: Not applicable

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

GCS-035PCM-SCP DISPENSIBLE PCM

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Causes skin irritation.
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: May cause genetic defects (inhalation).
Carcinogenicity	: May cause cancer (inhalation, oral).
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Acute aquatic toxicity	: Not classified
Chronic aquatic toxicity	: Not classified

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

GCS-035PCM-SCP DISPENSIBLE PCM

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

The following restrictions are applicable according to Annex XVII of the REACH Regulation (EC) No 1907/2006:

29. Substances which are classified as germ cell mutagen category 1A or 1B in Part 3 of Annex VI to Regulation (EC) No 1272/2008 and are listed in Appendix 3 or Appendix 4, respectively.	LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY
40. Substances classified as flammable gases category 1 or 2, flammable liquids categories 1, 2 or 3, flammable solids category 1 or 2, substances and mixtures which, in contact with water, emit flammable gases, category 1, 2 or 3, pyrophoric liquids category 1 or pyrophoric solids category 1, regardless of whether they appear in Part 3 of Annex VI to Regulation (EC) No 1272/2008 or not.	ALPHA ALUMINIUM OXIDE
28. Substances which are classified as carcinogen category 1A or 1B in Part 3 of Annex VI to Regulation (EC) No 1272/2008 and are listed in Appendix 1 or Appendix 2, respectively.	LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY
3. Liquid substances or mixtures which are regarded as dangerous in accordance with Directive 1999/45/EC or are fulfilling the criteria for any of the following hazard classes or categories set out in Annex I to Regulation (EC) No 1272/2008	LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY
3(b) Substances or mixtures fulfilling the criteria for any of the following hazard classes or categories set out in Annex I to Regulation (EC) No 1272/2008: Hazard classes 3.1 to 3.6, 3.7 adverse effects on sexual function and fertility or on development, 3.8 effects other than narcotic effects, 3.9 and 3.10	LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to REGULATION (EU) No 649/2012 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 4 July 2012 concerning the export and import of hazardous chemicals.

Substance(s) are not subject to Regulation (EC) No 850/2004 of the European Parliament and of the Council of 29 April 2004 on persistent organic pollutants and amending Directive 79/117/EEC.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Full text of H- and EUH-statements:	
Asp. Tox. 1	Aspiration hazard, Category 1
Carc. 1B	Carcinogenicity, Category 1B
Flam. Sol. 1	Flammable solids, Category 1
Muta. 1B	Germ cell mutagenicity, Category 1B

GCS-035PCM-SCP DISPENSIBLE PCM

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Skin Irrit. 2	Skin corrosion/irritation, Category 2
H228	Flammable solid.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H340	May cause genetic defects.
H350	May cause cancer.

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product