



**Part Number :** [14600121](#)

**Product Description :** 2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version A, Non-polarized, Wire Size 24 AWG, 3.81µm Tin/Lead (SnPb), 12 Circuits

**Series Number :** 70400

**Status :** Active

**Product Category :** Connector Housings

**Engineering Number :** 70400-0011



---

## Documents & Resources

### Drawings

[014600121\\_sd.pdf](#)

[PK-70873-0001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Active
Category	Connector Housings
Series	70400
Description	2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version A, Non-polarized, Wire Size 24 AWG, 3.81µm Tin/Lead (SnPb), 12 Circuits
Comments	Terminals Preloaded
Component Type	Housing
Product Name	SL
UPC	800754994224

**Agency**

CSA	LR19980
UL	E29179

**Electrical**

Voltage - Maximum	250V
-------------------	------

**Physical**

Circuits (Loaded)	12
Color - Resin	Black
Durability (mating cycles max)	25
Entry Angle	Vertical
Flammability	94V-0

Gender	Female
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Number of Rows	1
Packaging Type	Tube
PCB Retention	None
Pitch - Mating Interface	2.54mm
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Polarized to Mating Part	No
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	IDT or Pierce
Wire/Cable Type	Discrete Wire, Ribbon Cable
Wire Insulation Diameter	1.35mm max.
Wire Size (AWG)	24

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
KK 254 Vertical Breakaway Headers with Friction Lock	<a href="#"><u>42375</u></a>
KK 254 Right-Angle Surface Mount Compatible Breakaway Headers	<a href="#"><u>42377</u></a>

---

## Application Tooling

### Global

Description	Part Number

Ribbon Cable Tool Kit, Press Not Included	<u>622016600</u>
--	------------------

---

This document was generated on Aug 04, 2025