


Product datasheet

Specifications



clamping claws, PAS43, nut 6 - 10 pieces

VW33MF10613

EAN Code: 3606485228990

Main

Range of product	Lexium linear motion
Product or component type	Clamping jaw
Product specific application	To mount portal axis on fixed support
Accessory / separate part category	Maintenance accessories

Complementary

Product compatibility	PAS 43 linear axis, outer dimension : 80 x 80 mm
Range compatibility	Lexium PAS

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	13.100 cm
Package 1 Length	19.300 cm
Package 1 Weight	766.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	10.612 kg
Unit Type of Package 3	S06
Number of Units in Package 3	36
Package 3 Height	73.500 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	40.504 kg

Logistical informations

Country of origin	DE
-------------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold
PVC free	Yes

Use Longer


Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Take-back	No

Dimensions Drawings

Dimensions



Dimensions in mm

A	B	B1	B2	H	H1	L	L1	ØD1	ØD2
18	24	16	8	21.5	6.4	76	40	11	6.6

Dimensions in in.

A	B	B1	B2	H	H1	L	L1	ØD1	ØD2
0.71	0.94	0.63	0.31	0.85	0.25	2.99	1.57	0.43	0.26