


Geberit Mapress Stainless Steel ball valve with actuator lever and hose connector, flanged





Example image

APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For service water and process water
- For treated water (application range according to Technical Information „Treated water“)
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For compressed air (oil purity class 0–3)

CHARACTERISTICS

- Threaded nipple made of brass, with screw cap
- Spindle caulk made of PTFE
- Section seal of flange and ball made of PTFE
- Fulfils requirements in accordance with TA Air VDI 2440
- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating temperature

-20 – +120 °C

Product material

CrNiMo steel 1.4401 (EN 10088)

ACCESSORIES

- Actuator lever set, lockable, for Geberit Mapress ball valve, flanged

Art. no.	DNV	DN	d, ø mm	G "	L cm	L1 cm	L2 cm	Z cm	Z1 cm	PN bar
92110	15	12	15	3/4	12.7	5	9.3	4.1	4.1	40
92112	20	20	22	1	13.6	5.6	10.3	4.5	4.2	40