




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.34 – 2.5 mm²**

Mating Tab Width: **2.8 mm [.11 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	16.1 mm[.634 in]
Compatible Insulation Diameter Range	1.5 – 2.5 mm[.059 – .098 in]
Terminal Material Thickness	.25 mm[.01 in]
Wire Size	.34 – 2.5 mm ²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	12000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2150049-2 OCEAN-2.0-APPLICATOR-E-062F090FA-REA	 KIT TE Part # 7-2150636-7 OCEAN_2.0_SPARE_PART_KIT-062F090OV	 TE Part # 2150636-1 OCEAN-2.0-APPLICATOR-E-062F090OV-REM	 TE Part # 2150049-1 OCEAN-2.0-APPLICATOR-E-062F090F-REM
 KIT TE Part # 7-2150049-7 OCEAN_2.0_SPARE_PART_KIT-062F090F	 TE Part # 737107-4 110 FASTON REC 20-17 AWG TPBR	 TE Part # 2150636-2 OCEAN-2.0-APPLICATOR-E-062F090OV-REA	 TE Part # 141939-1 110 FASTON, FLAG, REC., 22-18 AWG, BR

Also in the Series | FASTON 110


 Crimp Terminal Housings(13)	 Insertion & Extraction Tools(1)	 PCB Terminals(22)	 Quick Disconnects(165)
---------------------------------	-------------------------------------	-----------------------	----------------------------

Customers Also Bought





TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
WedgeLocks: DEUTSCH DT

Documents

Product Drawings

110 FASTON,REC.,22-18 AWG,BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_140825-1_AS.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_140825-1_AS.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_140825-1_AS.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Wire Preparation And Crimp Inspection Guide

English

Agency Approvals

Agency Approval Document

English