




Connectors > PCB Connectors > Board-to-Board Connectors > PC/104 Connectors



Number of Positions: 104

Centerline (Pitch): 2.54 mm [.1 in]

Number of Loaded Positions: 102

Contact Current Rating (Max): 3 A

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board

Configuration Features

Stacking Configuration	Stack Through
Keying & Polarized Position Locations	B-10, C-19
Number of Standoffs	2
Number of Positions	104
Number of Loaded Positions	102

Electrical Characteristics

Insulation Resistance	1000 MΩ
Dielectric Withstanding Voltage (Max)	500 VAC

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------



Termination Post & Tail Length	12.27 mm[.483 in]
--------------------------------	-------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
PCB Mount Retention Type	Action/Compliant Tail
Mating Alignment Type	Keyed
Mating Alignment	With

Housing Features

Housing Material	Nylon - GF
Centerline (Pitch)	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Assembly Process Feature	Board Standoff
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1375793-3
ASSY, 64/40 POS PC104 LF

Also in the Series | AMPMODU PC/104

Card Edge Power Connectors(1)

Hand Crimping Tools(1)

PC/104 Connectors(25)

Rack & Panel Connectors(1)

Rectangular Connector Housings(1)

Rectangular Power Connectors(1)

Standard Rectangular Connectors(1)

Customers Also Bought

TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts

TE Part #DT04-2P
REC, 2P, GRY, N

TE Part #DT06-2S
PLG, 2P, GRY, N

TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



Documents

Product Drawings
ASSY, 64/40 POS PC104
English

CAD Files
Customer View Model
ENG_CVM_1375793-1_F.3d_igs.zip
English
Customer View Model
ENG_CVM_1375793-1_F.3d_stp.zip
English
Customer View Model
ENG_CVM_1375793-1_F.2d_dxf.zip
English
3D PDF
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
AMPMODU_INTERCONNECTION_SYSTEM_SECTION1AND2
English

Product Specifications
Application Specification
English

Agency Approvals
UL Report
English
UL Report
English