


**Tarauds machine Pas Métrique Hélicoïdaux**

|                    |                             |
|--------------------|-----------------------------|
| <b>Tolérance</b>   | ISO 2 - 6H                  |
| <b>Traitement</b>  | Brillant                    |
| <b>Entrée</b>      | Courte = 2 filets           |
| <b>Géométrie</b>   | Hélice 40° à droite         |
| <b>Utilisation</b> | Trous borgnes jusqu'à 2 x D |


**Maschinengewindebohrer M, 40° rechtsgedrallt**

|                     |                                                |
|---------------------|------------------------------------------------|
| <b>Toleranz</b>     | 6H-ISO 2                                       |
| <b>Oberfläche</b>   | Blank                                          |
| <b>Anschnitt</b>    | 2-3 Gang, Form C                               |
| <b>Spiralwinkel</b> | rechtsgedrallt, rechtsschneidend               |
| <b>Anwendung</b>    | Kurzer, stabiler Gewindebohrer für Sacklöcher. |


**Machinetappen M, 40° spiraal**

|                       |                                                                    |
|-----------------------|--------------------------------------------------------------------|
| <b>Tolerantie</b>     | ISO 2                                                              |
| <b>Oppervlaktebeh</b> | Blank / Blue = Stoomontlaten                                       |
| <b>Aansnijding</b>    | 3                                                                  |
| <b>Spaangroef</b>     | rechtse spiraal                                                    |
| <b>Toepassing</b>     | Machinetap voor doorlopende en blinde gaten tot draaddiepte 2 x D. |

| Entry Code   | M   | P mm | l <sub>1</sub> mm | l <sub>2</sub> mm | d <sub>2</sub> Ø mm | ∇ a mm | l <sub>3</sub> mm |
|--------------|-----|------|-------------------|-------------------|---------------------|--------|-------------------|
| E507M2       | 2   | 0,40 | 41                | 8                 | 2,50                | 2,00   | 4                 |
| E507M2BLUE   | 2   | 0,40 | 41                | 8                 | 2,50                | 2,00   | 4                 |
| E507M2.5     | 2,5 | 0,45 | 44,5              | 9,5               | 2,80                | 2,24   | 5                 |
| E507M2.5BLUE | 2,5 | 0,45 | 44,5              | 9,5               | 2,80                | 2,24   | 5                 |
| E507M3       | 3   | 0,50 | 48                | 12,5              | 3,15                | 2,50   | 5                 |
| E507M3BLUE   | 3   | 0,50 | 48                | 12,5              | 3,15                | 2,50   | 5                 |
| E507M3.5     | 3,5 | 0,60 | 50                | 14                | 3,55                | 2,80   | 5                 |
| E507M3.5BLUE | 3,5 | 0,60 | 50                | 14                | 3,55                | 2,80   | 5                 |
| E507M4       | 4   | 0,70 | 53                | 14                | 4,00                | 3,15   | 6                 |
| E507M4BLUE   | 4   | 0,70 | 53                | 14                | 4,00                | 3,15   | 6                 |
| E507M5       | 5   | 0,80 | 58                | 11                | 5,00                | 4,00   | 7                 |
| E507M5BLUE   | 5   | 0,80 | 58                | 11                | 5,00                | 4,00   | 7                 |
| E507M6       | 6   | 1,00 | 66                | 13                | 6,30                | 5,00   | 8                 |
| E507M6BLUE   | 6   | 1,00 | 66                | 13                | 6,30                | 5,00   | 8                 |
| E507M7       | 7   | 1,00 | 66                | 13                | 6,30                | 5,00   | 8                 |
| E507M7BLUE   | 7   | 1,00 | 66                | 13                | 6,30                | 5,00   | 8                 |
| E507M8       | 8   | 1,25 | 72                | 16                | 8,00                | 6,30   | 9                 |
| E507M8BLUE   | 8   | 1,25 | 72                | 16                | 8,00                | 6,30   | 9                 |

| Entry Code  | M  | P mm | l <sub>1</sub> mm | l <sub>2</sub> mm | d <sub>2</sub> Ø mm | ∇ a mm | l <sub>3</sub> mm |
|-------------|----|------|-------------------|-------------------|---------------------|--------|-------------------|
| E507M10     | 10 | 1,50 | 80                | 18                | 10,00               | 8,00   | 11                |
| E507M10BLUE | 10 | 1,50 | 80                | 18                | 10,00               | 8,00   | 11                |
| E507M12     | 12 | 1,75 | 89                | 22                | 9,00                | 7,10   | 10                |
| E507M12BLUE | 12 | 1,75 | 89                | 22                | 9,00                | 7,10   | 10                |
| E507M14     | 14 | 2,00 | 95                | 24                | 11,20               | 9,00   | 12                |
| E507M14BLUE | 14 | 2,00 | 95                | 24                | 11,20               | 9,00   | 12                |
| E507M16     | 16 | 2,00 | 102               | 24                | 12,50               | 10,00  | 13                |
| E507M16BLUE | 16 | 2,00 | 102               | 24                | 12,50               | 10,00  | 13                |
| E507M18     | 18 | 2,50 | 112               | 29                | 14,00               | 11,20  | 14                |
| E507M18BLUE | 18 | 2,50 | 112               | 29                | 14,00               | 11,20  | 14                |
| E507M20     | 20 | 2,50 | 112               | 29                | 14,00               | 11,20  | 14                |
| E507M20BLUE | 20 | 2,50 | 112               | 29                | 14,00               | 11,20  | 14                |
| E507M22     | 22 | 2,50 | 118               | 29                | 16,00               | 12,50  | 16                |
| E507M22BLUE | 22 | 2,50 | 118               | 29                | 16,00               | 12,50  | 16                |
| E507M24     | 24 | 3,00 | 130               | 35                | 18,00               | 14,00  | 18                |
| E507M24BLUE | 24 | 3,00 | 130               | 35                | 18,00               | 14,00  | 18                |