

# guided drive DFM-32-200-P-A-KF


Part number: 170938

★ Core product range

FESTO

With integrated guide.

The proximity switch, type SMTSO-8E, can be used with this product with stroke lengths equal to or greater than 50 mm. The corresponding mounting kit, type SMB-8E, is mounted inwardly or outwardly.



## Data sheet

Feature	Value
Centre of gravity distance from working load to yoke plate	50 mm
Stroke	200 mm
Piston diameter	32 mm
Operating mode of drive unit	Yoke
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide
Position detection	For proximity sensor
Operating pressure	1.5 ... 10 bar
Max. speed	0.8 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
Ambient temperature	-5 ... 60 °C
Impact energy in end positions	0.4 Nm
Max. force F <sub>y</sub>	1,130 N
Max. force F <sub>y</sub> static	1,260 N
Max. force F <sub>z</sub>	1,130 N
Max. force F <sub>z</sub> static	1,260 N
Max. torque M <sub>x</sub>	44.09 Nm
Max. torque M <sub>x</sub> static	49.14 Nm
Max. torque M <sub>y</sub>	40.13 Nm
Max. torque M <sub>y</sub> static	44.73 Nm
Max. torque M <sub>z</sub>	40.13 Nm
Max. torque M <sub>z</sub> static	44.73 Nm
Max. permissible torque load M <sub>x</sub> as a function of the stroke	5.76 Nm
Max. useful load as a function of the stroke at defined distance x <sub>s</sub>	127 N
Theoretical force at 6 bar, return stroke	415 N
Theoretical force at 6 bar, advance stroke	482 N
Moving mass	1,720 g
Product weight	4,249 g
Centre of gravity of the moving mass as a function of the stroke	114.6 mm
alternative connections	See product drawing
Pneumatic connection	G1/8
Materials note	Free of copper and PTFE Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	NBR
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive