



The Professional's Choice

SAFETY DATA SHEET

1. IDENTIFICATION OF THE MATERIAL AND SUPPLIER

1.1 Product identifier

Product name AIR BRUSH
Synonyms 2066 - PRODUCT CODE • 2067 - PRODUCT CODE • AIRBRUSH • CRC AIR BRUSH

1.2 Uses and uses advised against

Uses AIR BLOWER • BLOWING AGENT

1.3 Details of the supplier of the product

Supplier name CRC INDUSTRIES (AUST) PTY LIMITED
Address 9 Gladstone Road, Castle Hill, NSW, 2154, AUSTRALIA
Telephone (02) 9849 6700
Fax (02) 9680 4914
Email info.au@crcind.com
Website www.crcindustries.com.au

1.4 Emergency telephone numbers

Emergency 13 11 26 (PIC)

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

CLASSIFIED AS HAZARDOUS ACCORDING TO SAFE WORK AUSTRALIA CRITERIA

Physical Hazards

Aerosols - Pressurised: Category 3

Health Hazards

Not classified as a Health Hazard

Environmental Hazards

Not classified as an Environmental Hazard

2.2 GHS Label elements

Signal word WARNING

Pictograms

Hazard statements

H229 Pressurized container: may burst if heated.

Prevention statements

P210 Keep away from heat/sparks/open flames/hot surfaces. No smoking.
P251 Pressurized container: Do not pierce or burn, even after use.

Response statements

None allocated.

Storage statements

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C.

Disposal statements

None allocated.

2.3 Other hazards

No information provided.

3. COMPOSITION/ INFORMATION ON INGREDIENTS

3.1 Substances / Mixtures

Ingredient	CAS Number	EC Number	Content
1,1,1,2-TETRAFLUOROETHANE (HFC 134A)	811-97-2	212-377-0	>60%

4. FIRST AID MEASURES

4.1 Description of first aid measures

Eye If in eyes, hold eyelids apart and flush continuously with running water. Continue flushing until advised to stop by a Poisons Information Centre, a doctor, or for at least 15 minutes.

Inhalation If inhaled, remove from contaminated area. To protect rescuer, use an Air-line respirator where an inhalation risk exists. Apply artificial respiration if not breathing.

Skin Cold burns: Remove contaminated clothing and gently flush affected areas with warm water (30°C) for 15 minutes. It is recommended that warm water is applied to clothing before removing it so as to prevent further skin damage. Apply sterile dressing and treat as for a thermal burn. For large burns, immerse in warm water for 15 minutes. DO NOT apply any form of direct heat. Seek immediate medical attention.

Ingestion For advice, contact a Poisons Information Centre on 13 11 26 (Australia Wide) or a doctor (at once). If swallowed, do not induce vomiting.

First aid facilities None allocated.

4.2 Most important symptoms and effects, both acute and delayed

Contact with liquid may cause cold burns/frostbite.

4.3 Immediate medical attention and special treatment needed

Treat symptomatically.

5. FIRE FIGHTING MEASURES

5.1 Extinguishing media

Use an extinguishing agent suitable for the surrounding fire.

5.2 Special hazards arising from the substance or mixture

Non flammable. May evolve toxic gases (carbon oxides, hydrogen fluoride, hydrocarbons) when heated strongly.

5.3 Advice for firefighters

Evacuate area and contact emergency services. Toxic gases may be evolved in a fire situation. Remain upwind and notify those downwind of hazard. Wear full protective equipment including Self Contained Breathing Apparatus (SCBA) when combating fire. Use waterfog to cool intact containers and nearby storage areas.

5.4 Hazchem code

2Y
2 Fine Water Spray.
Y Risk of violent reaction or explosion. Wear full fire kit and breathing apparatus. Contain spill and run-off.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Wear Personal Protective Equipment (PPE) as detailed in section 8 of the SDS. Clear area of all unprotected personnel. Ventilate area where possible.

6.2 Environmental precautions

Prevent product from entering drains and waterways.

6.3 Methods of cleaning up

Contain spillage, then cover / absorb spill with non-combustible absorbent material (vermiculite, sand, or similar), collect and place in suitable containers for disposal.

6.4 Reference to other sections

See Sections 8 and 13 for exposure controls and disposal.

7. HANDLING AND STORAGE

7.1 Precautions for safe handling

Before use carefully read the product label. Use of safe work practices are recommended to avoid eye or skin contact and inhalation. Observe good personal hygiene, including washing hands before eating. Prohibit eating, drinking and smoking in contaminated areas.

7.2 Conditions for safe storage, including any incompatibilities

Store in a cool, dry, well ventilated area, removed from incompatible substances, heat or ignition sources and foodstuffs. Aerosol containers may explode if exposed to excessive heat (> 50°C). Ensure containers are adequately labelled and protected from physical damage when not in use.

7.3 Specific end uses

No information provided.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

8.1 Control parameters

Exposure standards

Ingredient	Reference	TWA		STEL	
		ppm	mg/m ³	ppm	mg/m ³
1,1,1,2-Tetrafluoroethane	SWA [AUS]	1000	4240	--	--

Biological limits

No biological limit values have been entered for this product.

8.2 Exposure controls

Engineering controls Avoid inhalation. Use in well ventilated areas. Where an inhalation risk exists, mechanical extraction ventilation is recommended. Maintain vapour levels below the recommended exposure standard.

PPE

- Eye / Face** Wear splash-proof goggles.
- Hands** Wear leather gloves.
- Body** When using large quantities or where heavy contamination is likely, wear coveralls.
- Respiratory** Where an inhalation risk exists, wear a Type A-Class P1 (Organic gases/vapours and Particulate) respirator. At high vapour levels, wear an Air-line respirator.



9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Appearance	COLOURLESS GAS (AEROSOL DISPENSED)
Odour	SLIGHT ETHEREAL ODOUR
Flammability	NON FLAMMABLE
Flash point	NOT RELEVANT
Boiling point	NOT AVAILABLE
Melting point	-26.4°C
Evaporation rate	NOT AVAILABLE
pH	NOT AVAILABLE
Vapour density	> 1 (Air = 1)
Specific gravity	1.212
Solubility (water)	NOT AVAILABLE
Vapour pressure	0.583 MPa @ 25°C
Upper explosion limit	NOT RELEVANT

9.1 Information on basic physical and chemical properties

Lower explosion limit	NOT RELEVANT
Partition coefficient	NOT AVAILABLE
Autoignition temperature	NOT AVAILABLE
Decomposition temperature	NOT AVAILABLE
Viscosity	NOT AVAILABLE
Explosive properties	NOT AVAILABLE
Oxidising properties	NOT AVAILABLE
Odour threshold	NOT AVAILABLE

9.2 Other information

% Volatiles	100 %
-------------	-------

10. STABILITY AND REACTIVITY

10.1 Reactivity

Carefully review all information provided in sections 10.2 to 10.6.

10.2 Chemical stability

Stable under recommended conditions of storage.

10.3 Possibility of hazardous reactions

Polymerization is not expected to occur.

10.4 Conditions to avoid

Avoid heat, sparks, open flames and other ignition sources.

10.5 Incompatible materials

Incompatible with oxidising agents (e.g. hypochlorites), alkalis (e.g. sodium hydroxide) and alkaline earth metals (e.g. manganese).

10.6 Hazardous decomposition products

May evolve toxic gases if heated to decomposition.

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity This product is expected to be of low toxicity. Based on available data, the classification criteria are not met. This product may have the potential to cause adverse health effects if intentionally misused (e.g. deliberately inhaling contents).

Information available for the ingredients:

Ingredient	Oral LD50	Dermal LD50	Inhalation LC50
1,1,1,2-TETRAFLUOROETHANE (HFC 134A)	--	--	1500 g/m ³ /4 hour (rat)

Skin	Not classified as a skin irritant. Contact with the liquefied material or escaping compressed gas may cause frostbite injury.
Eye	Not classified as an eye irritant. Contact with the liquefied material or escaping compressed gas may cause frostbite injury.
Sensitisation	Not classified as causing skin or respiratory sensitisation.
Mutagenicity	Not classified as a mutagen.
Carcinogenicity	Not classified as a carcinogen.
Reproductive	Not classified as a reproductive toxin.
STOT - single exposure	Asphyxiant. Effects are proportional to oxygen displacement. Over exposure may result in dizziness, drowsiness, weakness, fatigue, breathing difficulties and unconsciousness.
STOT - repeated exposure	Not classified as causing organ damage from repeated exposure.
Aspiration	Ingestion is considered unlikely due to product form.

12. ECOLOGICAL INFORMATION

12.1 Toxicity

No information provided.

12.2 Persistence and degradability

No information provided.

12.3 Bioaccumulative potential

No information provided.

12.4 Mobility in soil

No information provided.

12.5 Other adverse effects

No information provided.

13. DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Waste disposal For small amounts, absorb contents with sand or similar and dispose of to an approved landfill site. Do not puncture or incinerate aerosol cans. Contact the manufacturer/supplier for additional information (if required).

Legislation Dispose of in accordance with relevant local legislation.

14. TRANSPORT INFORMATION

CLASSIFIED AS A DANGEROUS GOOD BY THE CRITERIA OF THE ADG CODE



	LAND TRANSPORT (ADG)	SEA TRANSPORT (IMDG / IMO)	AIR TRANSPORT (IATA / ICAO)
14.1 UN Number	1950	1950	1950
14.2 Proper Shipping Name	AEROSOLS	AEROSOLS	AEROSOLS
14.3 Transport hazard class	2.2	2.2	2.2
14.4 Packing Group	None allocated.	None allocated.	None allocated.

14.5 Environmental hazards

No information provided.

14.6 Special precautions for user

Hazchem code 2Y
GTEPG 2C1
EmS F-D, S-U

15. REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Poison schedule A poison schedule number has not been allocated to this product using the criteria in the Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP).

Classifications Safework Australia criteria is based on the Globally Harmonised System (GHS) of Classification and Labelling of Chemicals.

Inventory listings **AUSTRALIA: AIIC (Australian Inventory of Industrial Chemicals)**
All components are listed on AIIC, or are exempt.

16. OTHER INFORMATION

Additional information

PERSONAL PROTECTIVE EQUIPMENT GUIDELINES:

The recommendation for protective equipment contained within this report is provided as a guide only. Factors such as form of product, method of application, working environment, quantity used, product concentration and the availability of engineering controls should be considered before final selection of personal protective equipment is made.

HEALTH EFFECTS FROM EXPOSURE:

It should be noted that the effects from exposure to this product will depend on several factors including: form of product; frequency and duration of use; quantity used; effectiveness of control measures; protective equipment used and method of application. Given that it is impractical to prepare a report which would encompass all possible scenarios, it is anticipated that users will assess the risks and apply control methods where appropriate.

Abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS #	Chemical Abstract Service number - used to uniquely identify chemical compounds
CNS	Central Nervous System
EC No.	EC No - European Community Number
EMS	Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)
GHS	Globally Harmonized System
GTEPG	Group Text Emergency Procedure Guide
IARC	International Agency for Research on Cancer
LC50	Lethal Concentration, 50% / Median Lethal Concentration
LD50	Lethal Dose, 50% / Median Lethal Dose
mg/m ³	Milligrams per Cubic Metre
OEL	Occupational Exposure Limit
pH	relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).
ppm	Parts Per Million
STEL	Short-Term Exposure Limit
STOT-RE	Specific target organ toxicity (repeated exposure)
STOT-SE	Specific target organ toxicity (single exposure)
SUSMP	Standard for the Uniform Scheduling of Medicines and Poisons
SWA	Safe Work Australia
TLV	Threshold Limit Value
TWA	Time Weighted Average

Report status

This document has been compiled by RMT on behalf of the manufacturer, importer or supplier of the product and serves as their Safety Data Sheet ('SDS').

It is based on information concerning the product which has been provided to RMT by the manufacturer, importer or supplier or obtained from third party sources and is believed to represent the current state of knowledge as to the appropriate safety and handling precautions for the product at the time of issue. Further clarification regarding any aspect of the product should be obtained directly from the manufacturer, importer or supplier.

While RMT has taken all due care to include accurate and up-to-date information in this SDS, it does not provide any warranty as to accuracy or completeness. As far as lawfully possible, RMT accepts no liability for any loss, injury or damage (including consequential loss) which may be suffered or incurred by any person as a consequence of their reliance on the information contained in this SDS.

Prepared by

Risk Management Technologies
 5 Ventnor Ave, West Perth
 Western Australia 6005
 Phone: +61 8 9322 1711
 Fax: +61 8 9322 1794
 Email: info@rmt.com.au
 Web: www.rmtglobal.com

[End of SDS]