

ALL CERAMIC CRYSTAL RESONATORS (SMD)

SMAC-5032



FEATURES

- All ceramic epoxy sealed SMD package
- Wide frequency range
- 2 / 4 pads version available
- 100% Pb free

Request for samples / quotation

Part number descriptions

Where to buy




Item		Specifications
Nominal Frequency Range	f_0	10.0MHz ~ 48.0MHz (Fundamental)
Frequency Tolerance, $T_a=25^\circ\text{C} \pm 3^\circ\text{C}$	$\Delta f/f$	$\pm 20\text{ppm}$, $\pm 30\text{ppm}$, $\pm 50\text{ppm}$
Load Capacitance	C_L	18pF or customer specify
Frequency Tolerance over Operating Temperature Range	$\Delta f/f$	$\pm 20\text{ppm}$, $\pm 30\text{ppm}$, $\pm 50\text{ppm}$
Operating Temperature Range	T_{OPR}	$-20^\circ\text{C} \sim +70^\circ\text{C}$, $-40^\circ\text{C} \sim +85^\circ\text{C}$
Storage Temperature Range	T_{STG}	$-55^\circ\text{C} \sim +125^\circ\text{C}$
Drive Level	DL	0.1mW (0.5mW Max.)
Shunt Capacitance	C_0	7pF Max.
Insulation Resistance	IR	500M Ω Min.
Aging	Δf_A	$\pm 5\text{ppm/Year Max.}$

SERIES RESISTANCE (ESR)




Frequency Range	$10.000 < f_0 \leq 16.000$	$16.000 < f_0 \leq 48.000$
ESR	60 Ω Max.	30 Ω Max.

Please consult our sales representatives for other specifications.

DIMENSION (mm)



SOLDERING PATTERN (mm)



All specifications are subject to change without notice.



Interquip Electronics Co., Ltd

Flat A, 9/F, On Shing Industrial Building, 2-16 Wo Liu Hang Road, Fotan, Hong Kong
 Tel: +852 2413 5515 Fax: +852 2413 7053 <http://www.interquip.com>