



Temperature / mA converter

9113B

- Input for RTD, TC and mA
- Active / passive mA output via the same two terminals
- 1 or 2 channels
- Can be supplied separately or installed on power rail, PR type 9400
- SIL 2-certified via Full Assessment



Advanced features

- Configuration and monitoring by way of detachable display front (PR 4511/4501); process calibration and signal simulation.
- Copying of the configuration from one device to others of the same type via the display front.
- TC inputs can use either the internal CJC or a terminal with a built-in Pt100 sensor (PR 5910Ex, channel 1 / PR 5913Ex, channel 2) for higher accuracy.
- Advanced monitoring of internal communication and stored data.
- SIL 2 functionality is optional and must be activated in a menu point.

Application

- The device can be mounted in the safe area and in zone 2 / cl. 1 div. 2 and receive signals from zone 0, 1, 2 and zone 20, 21, 22 including M1 / Class I/II/III, Div. 1, Gr. A-G.
- Conversion and scaling of temperature (Pt, Ni and TC) and active current signals.
- The 9113 has been designed, developed and certified for use in SIL 2 applications according to the requirements of IEC 61508.


Technical characteristics

- 1 green and 2 red front LEDs indicate operation status and malfunction.
- 2.6 kVAC galvanic isolation between input, output and supply.

Mounting

- The devices can be mounted vertically or horizontally without distance between neighbouring units.

Applications



Order:

Type	Unit channels
9113B	Single : A
	Double : B

Environmental Conditions

Operating temperature.....	-20°C to +60°C
Storage temperature.....	-20°C to +85°C
Calibration temperature.....	20...28°C
Relative humidity.....	< 95% RH (non-cond.)
Protection degree.....	IP20
Installation in.....	Pollution degree 2 & measurement / overvoltage cat. II

Mechanical specifications

Dimensions (HxWxD).....	109 x 23.5 x 104 mm
Dimensions (HxWxD) w/ 4501 / 4511.....	109 x 23.5 x 116 / 131 mm
Weight approx.....	250 g
Weight incl. 4501 / 4511 (approx.).....	265 g / 350 g
DIN rail type.....	DIN EN 60715/35 mm
Wire size.....	0.13...2.08 mm ² AWG 26...14 stranded wire
Screw terminal torque.....	0.5 Nm
Vibration.....	IEC 60068-2-6
2...13.2 Hz.....	±1 mm
13.2...100 Hz.....	±0.7 g

Common specifications

Supply

Supply voltage.....	19.2...31.2 VDC
Fuse.....	400 mA SB / 250 VAC
Max. required power.....	≤ 0.8 W / ≤ 1.4 W (1 ch. / 2 ch.)
Max. power dissipation, 1 / 2 ch.....	≤ 0.8 W / ≤ 1.4 W

Isolation voltage

Test /working: Input to any.....	2.6 kVAC / 300 VAC reinforced isolation
Analog output to supply.....	2.6 kVAC / 300 VAC reinforced isolation
Status relay to supply.....	1.5 kVAC / 150 VAC reinforced isolation

Response time

Temperature input, programmable (0...90%, 100...10%).....	1...60 s
mA / V input (programmable).....	0.4...60 s

Programming..... Communication enabler 4511 / Programming front 4501

Signal / noise ratio.....	Min. 60 dB (0...100 kHz)
Signal dynamics, input.....	24 bit
Signal dynamics, output.....	16 bit
Accuracy.....	Better than 0.1% of selected range

EMC immunity influence.....	< ±0.5% of span
Extended EMC immunity: NAMUR NE21, A criterion, burst.....	< ±1% of span

Input specifications

RTD input

RTD type.....	Pt10/20/50/100/200/250/300/PT400/500/1000; Ni50/100/120/1000
---------------	--

Cable resistance per wire (max.).....	50 Ω
Sensor current.....	Nom. 0.2 mA
Effect of sensor cable resistance (3-/4-wire).....	< 0.002 Ω / Ω

Sensor error detection..... Programmable ON / OFF

TC input

Thermocouple type..... B, E, J, K, L, N, R, S, T, U, W3, W5, LR

Cold junction compensation (CJC) via ext. sensor in connector 5910..... 20...28°C ≤ ±1°C, -20...20°C / 28...70°C ≤ 2°C

CJC via internally mounted sensor..... ±(2.0°C + 0.4°C * Δt)
 Δt = Internal temp.-ambient temp.
 Sensor error detection..... Programmable ON or OFF (only wire breakage)

Sensor error current: When detecting / else..... Nom. 2 μA / 0 μA

Current input

Measurement range..... 0...23 mA
 Programmable measurement ranges..... 0...20 and 4...20 mA
 Input resistance..... Nom. 20 Ω + PTC 50 Ω
 Sensor error detection..... Programmable ON / OFF

Output specifications

Current output

Signal range..... 0...23 mA
 Programmable signal ranges..... 0...20/4...20/20...0/20...4 mA
 Load (@ current output)..... ≤ 600 Ω
 Load stability..... ≤ 0.01% of span / 100 Ω
 Sensor error indication..... 0 / 3.5 / 23 mA / none
 NAMUR NE43 Upscale/Downscale..... 23 mA / 3.5 mA
 Output limitation, on 4...20 and 20...4 mA signals..... 3.8...20.5 mA
 Output limitation, on 0...20 and 20...0 mA signals..... 0...20.5 mA
 Current limit..... ≤ 28 mA

Passive 2-wire mA output

Max. external 2-wire supply..... 26 VDC
 Max. load resistance [Ω]..... (Vsupply-3.5)/0.023 A
 Effect of external 2-wire supply voltage variation..... < 0.005% of span / V

Status relay

Max. voltage..... 110 VDC / 125 VAC
 Max. current..... 0.3 ADC / 0.5 AAC
 Max. AC power..... 62.5 VA / 32 W

Observed authority requirements

EMC.....	2014/30/EU
LVD.....	2014/35/EU
RoHS.....	2011/65/EU
EAC.....	TR-CU 020/2011

Approvals

ATEX 2014/34/EU.....	KEMA 07ATEX0148 X
IECEx.....	KEM 09.0052X
FM.....	3038279-C
INMETRO.....	DEKRA 16.0003 X
UL.....	UL 61010-1
EAC Ex TR-CU 012/2011.....	RU C-DK.GB08.V.00410
DNV-GL Marine.....	Stand. f. Certific. No. 2.4
CCOE.....	P337349/3
SIL.....	SIL 2 certified & fully assessed acc. to IEC 61508