Product data sheet Characteristics

XCSB803

metal safety switch XCSB - 3 NC - slow break - 1 entry tapped 1/2" NPT





Main

| Range of product | Telemecanique Safety switches XCS |
|-------------------------------|---|
| Product or component type | Safety switch |
| Component name | XCSB |
| Design | Industrial |
| Material | Metal |
| Head type | Key operated turret head |
| Contacts type and composition | 3 NC |
| Contact operation | Slow-break, simultaneous |
| Cable entry | 1 entry tapped for 1/2" NPT |
| Electrical connection | Terminal, clamping capacity: 1 x 0.52 x 1.5 mm² with or without cable end |
| Number of poles | 3 |
| Locking options description | With locking of actuator, unlocking by push-button |
| Local signalling | Without |
| | |

Complementary

| Complementary | |
|--|---|
| Positive opening | With NC contact |
| Mechanical durability | 600000 Cycles |
| Minimum actuation speed | 0.01 M/S |
| Maximum actuation speed | 0.5 M/S |
| [le] rated operational current | 6 A at 120 V, AC-15, A300 conforming to EN/IEC 60947-5-1 3 A at 240 V, AC-15, A300 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 |
| [Ithe] conventional enclosed thermal current | 10 A |
| [Ui] rated insulation voltage | 300 V conforming to UL 508 500 V conforming to EN/IEC 60947-1 300 V conforming to CSA C22.2 No 14 |
| [Uimp] rated impulse withstand voltage | EN/IEC 60947-5-1 6 kV |
| Short-circuit protection | 10 A cartridge fuse type gG (gl) |
| Actuator forcible withdrawal rtc | 1500 N |
| Minimum actuator force for extraction | 20 N |
| Maximum operating rate | 10 Cyc/Mn for maximum durability |
| Safety level | Can reach category 4 with the appropriate monitoring system and correctly wired-conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired-conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to EN/IEC 61508 |

| Safety reliability data | B10d = 5000000 value given for a life time of 20 years limited by mechanical or- contact wear |
|-------------------------|--|
| Body material | Zamak |
| Head material | Zamak |
| Depth | 44 Mm |
| Height | 114 Mm |
| Width | 52 Mm |
| Net weight | 0.475 Kg |

Environment

| Standards | EN 1088/ISO 14119 |
|---------------------------------------|--|
| | UL 508 |
| | EN/IEC 60204-1 |
| | EN/ISO 12100 |
| | EN/IEC 60947-5-1 |
| | CSA C22.2 No 14 |
| Product certifications | CSA |
| | UL |
| Protective treatment | TC |
| Ambient air temperature for operation | -2570 °C |
| Ambient air temperature for storage | -4070 °C |
| Vibration resistance | 5 gn (f= 10500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 10 gn for 11 ms conforming to IEC 60068-2-27 |
| Electrical shock protection class | Class I conforming to EN/IEC 61140 |
| IP degree of protection | IP67 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 |
| | |

Packing Units

| Package 1 Weight | 0.508 Kg | |
|------------------|----------|--|
| Package 1 Height | 1.220 Dm | |
| Package 1 width | 0.500 Dm | |
| Package 1 Length | 0.680 Dm | |

Offer Sustainability

| Onor Odotamasinty | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACh Regulation | ☑ REACh Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| RoHS exemption information | ₫Yes |
| Environmental Disclosure | Product Environmental Profile |
| | |

Contractual warranty

| | |
|-----------|-----------|
| 141 | |
| Warranty | 18 months |
| Trantanty | To monate |
| | |

Product Life Status : Commercialised

