




EMI & EMC Solutions > EMI Filters > Power Entry Modules



Filter Type: **Power Line**

Product Orientation: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **220 μ A**

Leakage Current (Max) (250VAC, 50Hz): **380 μ A**

Current Rating: **1 A**

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	Wire Lead
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	220 μ A
Leakage Current (Max) (250VAC, 50Hz)	380 μ A
Current Rating	1 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Right Angle
---------------------	-------------

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Usage Conditions



Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought




TE Part #2-2301994-3
RJ45 JACK INT.MAG. 1GB LED 1X1



TE Part #4-1879127-0
RN 0402 340R 0.1% 10PPM CUT LENGTH



TE Part #2307706-5
5P,2MM,B-B,REC,SRHZ,2.1,0.38AU,TR



TE Part #8-1415899-8
RZ01-1A3-D009



TE Part #T1280242132-000
H24B-TGBH-M32




TE Part #4-1618239-1
K41B932=RELAY, VACUUM, SPST-NC



TE Part #2-1624116-6
BMB-A 0603 40R N8



TE Part #2007793-3
IMP100S,H,V3P16C,LG,OEWS39,5.5



TE Part #1051810-1
SMA CABLE PLUG 2031 8125 92

Documents

Product Drawings
1EEJ8=F8007

English

- CAD Files
- Customer View Model
ENG_CVM_3-6609006-2_0.3d_igs.zip
- English
- Customer View Model
ENG_CVM_3-6609006-2_0.3d_stp.zip
- English
- Customer View Model
ENG_CVM_3-6609006-2_0.2d_dxf.zip
- English
- 3D PDF
- English
- Customer View Model
ENG_CVM_CVM_3-6609006-2_A.3d_igs.zip
- English

Customer View Model

[ENG_CVM_CVM_3-6609006-2_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-6609006-2_A.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_EEJ_SERIES](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English