

## Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and SLIVER

## RS PRO Fire Sleeve SLIVER 15m

RS Stock No.: 0733550



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

## General Specifications

Part Number	Ordering Size (mm)
0731298	4
0733712	6
0733713	8
0733714	10
0733715	12
0733530	14
0733531	16
0733532	19
0733533	22
0733534	25
0733535	28
0733537	32
0733538	35
0733539	38
0733540	41
0733541	51
0733543	57
0733544	63
0733545	70
0733546	76
0733547	83
0733548	89
0733549	95
0733550	102
0733551	114
0733552	127
0733553	140
0733555	168
0733556	180
0733557	203

## Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2