


1518070
<https://www.phoenixcontact.com/gb/products/1518070>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, PROFIBUS (12 Mbps), 2-position, PUR halogen-free, red lilac RAL 4001, shielded, free cable end, on Socket straight M12 SPEEDCON, coding: B, cable length: 5 m

Commercial data

Item number	1518070
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF1CKC
Product key	BF1CKC
Catalog page	Page 198 (C-6-2019)
GTIN	4017918968199
Weight per piece (including packing)	317 g
Weight per piece (excluding packing)	325.1 g
Customs tariff number	85444290
Country of origin	PL

SAC-2P- 5,0-910/FSB SCO - Bus system cable



1518070

<https://www.phoenixcontact.com/gb/products/1518070>

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard
Sensor type	PROFIBUS
Number of positions	2
No. of cable outlets	1
Shielded	yes
Coding	B

Data management status

Article revision	08
------------------	----

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Interfaces

Bus system	PROFIBUS
Signal type/category	PROFIBUS, 12 Mbps (max. 100 m)

Signaling

Status display	no
Status display present	No

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A
Transmission medium	Copper

Material specifications

Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Connection data

Pin assignment

Contact Color (signal designation) Contact (optional)	2 (Socket) GN (A cable)
---	---------------------------

SAC-2P- 5,0-910/FSB SCO - Bus system cable



1518070

<https://www.phoenixcontact.com/gb/products/1518070>

4 (Socket) | RD (B cable)

Connector

Connection 1

Type

free cable end

Connection 2

Type

free cable end

Cable/line

Cable length

5 m

PROFIBUS [910]

Dimensional drawing



Cable weight

90 kg/km

UL AWM Style

21198 (80°C/300 V)

Number of positions

2

Shielded

yes

Cable type

PROFIBUS [910]

Conductor structure

1x2xAWG24/19

Conductor structure signal line

19x 0.13 mm

AWG signal line

24

Conductor cross section

2x 0.25 mm² (Signal line)

Wire diameter incl. insulation

2.55 mm ±0.07 mm

External cable diameter

7.80 mm ±0.2 mm

Outer sheath, material

PUR

External sheath, color

red lilac RAL 4001

Conductor material

Tin-plated Cu litz wires

Material, filler

PP

Material wire insulation

Foam-Skin PP

Single wire, color

red, green

Overall twist

2 cores with 2 fillers to the core

Optical shield covering

85 %

Max. conductor resistance

≤ 78.6 Ω/km

Insulation resistance

≥ 5 GΩ*km

Wave impedance

150 Ω ±10 % (3 MHz ... 20 MHz)

Cable capacity

nom. 30 pF/m

SAC-2P- 5,0-910/FSB SCO - Bus system cable



1518070

<https://www.phoenixcontact.com/gb/products/1518070>

Nominal voltage, cable	300 V
Test voltage Core/Core	1500 V (50 Hz, 1 min.)
Test voltage Core/Shield	1500.00 V (50 Hz, 1 min.)
Smallest bending radius, fixed installation	40 mm
Smallest bending radius, movable installation	65 mm
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 65 mm, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s ² , Ambient temperature: -20 °C ... 60 °C
	Max. bending cycles: 5000000, Bending radius: 80 mm, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s ² , Ambient temperature: -20 °C ... 60 °C
Shield attenuation	≤ 0.049 dB/m (at 16 MHz)
Halogen-free	in accordance with DIN VDE 0472 part 815
	according to IEC 60754-1
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
	IEC 60332-1-2
Other resistance	Low adhesion
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)
	-20 °C ... 60 °C (for installation)
	-20 °C ... 60 °C (cable, drag chain applications)


Environmental and real-life conditions

Ambient conditions


Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

Drawings

Circuit diagram



Schematic diagram




Pin assignment M12 socket, 5-pos., B-coded, female side

SAC-2P- 5,0-910/FSB SCO - Bus system cable

1518070

<https://www.phoenixcontact.com/gb/products/1518070>

Dimensional drawing



M12 x 1 socket, straight, shielded

SAC-2P- 5,0-910/FSB SCO - Bus system cable



1518070

<https://www.phoenixcontact.com/gb/products/1518070>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1518070>

	UL Listed Approval ID: FILE E 221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	300 V	4 A	-	-

	cUL Listed Approval ID: FILE E 221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	300 V	4 A	-	-

	EAC-RoHS Approval ID: RU D-DE.HB35.B.00387			

cULus Listed				
---------------------	--	--	--	--

SAC-2P- 5,0-910/FSB SCO - Bus system cable



1518070

<https://www.phoenixcontact.com/gb/products/1518070>

Classifications

ECLASS

ECLASS-11.0	27060307
ECLASS-12.0	27060307
ECLASS-13.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-2P- 5,0-910/FSB SCO - Bus system cable



1518070
<https://www.phoenixcontact.com/gb/products/1518070>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	3.038 kg CO2e

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk