

40Vmax Edger XGT® UE001G

Model UE001G is a cordless edger with a straight shaft powered by a 40Vmax XGT® Li-Ion battery.

Introducing a dedicated edger one of the essential tools for landscapers. Feature and benefits: Output similar to 30cm³ class engine powered edger. IPX4 compatible allows you to operate the tool even in wet conditions. New lock off mechanism. Guard with high visibility of the blade. Active Feedback sensing Technology (AFT).



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 4800 min ⁻¹
Electronic brake	✓
Max Cutting Capacity	59 mm
Cutting width	203 mm
Anti-Restart Function (NVR Switch)	✓
Thread size	M10 x 1,25
Continuous use XGT® 40Vmax / 5.0 Ah	18 min
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Sound Power Level (L _{WA})	89,4 dB(A)
Sound Pressure Level (L _{pA})	75,5 dB(A)

User benefits

- Variable speed control dial enables user to match the speed to the application for greater versatility
- Constant speed control maintains constant speed under load
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Cutting depth adjustment
- Ergonomically designed new loop handle fits comfortably in user's hand

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing